

917 Receptacle angled rotatable

speedtec - ready 7-pin insulation insert 1,5mm², Code 3 (pin) Connection Cross Section to 1.5 mm² Earth-to-Housing Connection according to VDE 0627 flange mount /Flange 21x21 Anti-vibration o-ring

B ED C 878 NN 00 00 151A 000 B G C 878 N 00 00 151A 000



Contact Arrangement mating view



Technical Data 7 (6+PE) -20 °C to 130 °C temperature range when connected IP 66/67

Electrical Data rated current rated voltage rated insulation voltage (L-L)

number of pins

protection type

power

Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

pollution degree over voltage category max. height for operation

Material

mating cycles

housing insulation insert seals

zinc diecast / chromated PBT, UL 94 / V0 FKM

Contacts (not part of product contents)

Tools (not part of product contents)

© 2018 TE Connectivity


TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

E li

TE Connectivity Industrial GmbH Bernrieder Straße 15 94559 Niederwinkling, Deutschland Tel.: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mail: intercontec@te.com Web: www.intercontec.biz





Main Dimensions Receptacle angled rotatable

*for max. wire cross-section pay attention to the cross-section of used contacts

power max. 14 A* 630V (AC/DC) 6000 V

500

III

2000 m