

4

3

2

1

THIS DRAWING IS UNPUBLISHED.
DIFFUSION RESTREINTE

RELEASED FOR PUBLICATION
LIBRE A LA DIFFUSION

20




ALL RIGHTS RESERVED.
TOUS DROITS RESERVES

© COPYRIGHT 20 BY -

REVISIONS


P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
	A	CREATION	06DEC2016	JB	SS

COUPE A-A



BLMC-95/240-12-800A	2832257-1
DESCRIPTION	PART NUMBER

	AL			
	ROUND STRANDED /Rond câblé /RM	ROUND SOLID /Rond solide /RE	SECTOR STRANDED /Sectoral câblé /SM	SECTOR SOLID /Sectoral câblé /SE
CONDUCTOR CROSS-SECTION /Section conducteur /Querschnittsbereich mm ²	95-240	95-240	95-150 (185 and 240 with rounding)	95-150 (185 with 90°)
CONDUCTOR DIAMETER /Diamètre conducteur /Leiterdurchmesser mm	Ø 11-Ø 19.2	Ø 10.5-Ø 18	-	-
TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLERANCES NON SPECIFIEES:				-



THIS DRAWING IS A CONTROLLED DOCUMENT. CE PLAN EST UN DOCUMENT CONTROLE PAR TYCO ELECTRONICS CORPORATION. IL EST SUSCEPTIBLE D'ETRE REVISE. POUR OBTENIR LA DERNIERE REVISION, CONTACTER LE SERVICE TECHNIQUE DE TYCO ELECTRONICS SIMEL SAS, 21220 GEVREY-CHAMBERTIN, FRANCE.		DWN/DESSINE BERLAND	06DEC2016	 TE Connectivity	
DIMENSIONS: mm		CHK/VERIFIE MILLOT	-		
TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLERANCES NON SPECIFIEES: (SUIV NB DE DECIMALES): 0 PLC/DEC: ±0 1 PLC/DEC: ±0 2 PLC/DEC: ±0 3 PLC/DEC: ±0 4 PLC/DEC: ±0 ANGLES ±°		APVD/APPROUVE SHI	-	NAME TITRE BLMC-95-240-12-800A	
MATERIAL MATIERE AL ALLOY -		PRODUCT SPEC SPEC. PRODUIT -	-	SIZE FORMAT A3	
FINISH FINITION TINNED		APPLICATION SPEC SPEC. APPLICATION -	-	CAGE CODE 00779	DRAWING NO No PLAN C-2832257
WEIGHT MASSE APPROX. 231g		CUSTOMER DRAWING /PLAN CLIENT	UNIQUEMENT POUR REFERENCE	SCALE ECHELLE 1:1	SHEET FEUILLE OF DE REV A