


4805 (3/11)

MATERIAL: CONTACTS AND SHIELDS - COPPER ALLOY ORGANIZER - STAINLESS STEEL HOUSING, GROUND SHELLS, AND PIN SPACER - THERMOPLASTIC, UL 94V-0, BLACK


4

5

- 2 FINISH: - CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-32021 BASED ON TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III, APPLICATIONS IN CONTROLLED ENVIRONMENTS (CENTRAL OFFICE). - COMPLIANT PIN AREA: 0.5µm MIN MATTE TIN.
- 3 GROUND PLATED THRU HOLE REQUIREMENTS: FINISHED HOLE =  $\emptyset$  0.34±0.05 HOLE SIZE PRIOR TO PLATING =  $\emptyset$  0.420±0.025 COPPER THICKNESS = 0.025 MIN IMMERSION TIN IF APPLICABLE = 0.00095 REF
- 4 SIGNAL PLATED THRU HOLE REQUIREMENTS: FINISHED HOLE =  $\emptyset$  0.24±0.05 HOLE SIZE PRIOR TO PLATING =  $\emptyset$  0.320±0.025 COPPER THICKNESS = 0.025 MIN IMMERSION TIN IF APPLICABLE = 0.00095 REF
- ∠5 SI VIA PLATED THRU HOLE REQUIREMENTS: HOLE SIZE PRIOR TO PLATING=0.300 $\pm$ 0.025 COPPER THICKNESS= MIN REQUIRED TO MEET REQUIRED ELECTRICAL PERFORMANCE
- 6 SI VIAS & SIGNAL HOLES: PTH DIMENSIONS APPLY TO THE TOP I.00mm OF THE PCB THICKNESS FROM THE CONNECTOR MOUNTING SIDE. GROUND HOLES: PTH DIMENSIONS APPLY TO THE TOP 1.25mm OF THE PCB THICKNESS FROM THE
- CONNECTOR MOUNTING SIDE. CONNECTOR MARKED WITH PART NUMBER, DATE CODE, AND "100 OHM" IN APPROXIMATE AREA SHOWN.
- A DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- APPLIES TO FINISHED HOLE DIAMETER.
- DATAMATRIX BARCODE MARKING IN THIS AREA.



2			1		
GP 00	P LTR	REVISIONS	DATE	DWN	APVD
<u> </u>	D	REVISED PER ECO-19-006255	22APR2019	ΑP	RP
	E	REVISED PER ECO-19-006930	08MAY2019	ΑP	RP
	F	REVISED PER ECO-19-012865	20AUG2019	ΑP	RP
	G	REVISED PER ECO-21-003195	10MAR2021	ΑP	RP



С	ONTROLLED DOCUMENT.	J.K.SHOBER CHK 25NOV2013	TE Connectivity			
1	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±-	E.WICKES APVD - PRODUCT SPEC 108-32021 APPLICATION SPEC	R/A RECEPTACLE ASSEMBLY, 100 OHM 12 PAIR, 6 COLUMN, PAIR-IN-ROW, STRADA WHISPER			
	ANGLES ±-	4-32029 WEIGHT	SIZE CAGE CODE DRAWING NO A 1 00779 $C = 2187462$ -			
		Customer Drawing	SCALE I:I SHEET 2 2 REV G			