



- NOTES:
1. The cumulative allowable tolerance of the distance between ten holes of the round hole is $\pm 0.2\text{mm}$
 2. The length of the belt is 250mm and the allowable bending degree is 1mm
 3. The thickness of the material is measured at the edge of the carrier tape
 4. All size definitions follow the definitions of EIA-481-C series standards
 5. Material: black PS T=0.30mm
 6. All reels are gray and blue hollowed out rotating plastic reels
 7. The non-specified tolerance range is: $\pm 0.1\text{mm}$; the cumulative error is not calculated if it exceeds 250mm.
 8. Molding length: 12.576mm
 9. The chamfer R where the shape of the cavity is not marked is 0.2-0.3; if the draft angle is not marked, it is below 3°