

THIS DRAWING IS UNPUBLISHED.





RELEASED FOR PUBLICATION

© COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	CORRECT TYPO	22JUN2022	DC	CY



ADHESIVE CUT LINE

- FABRICATE TO MEET IPC - 6013, CLASS 2.
INSPECT TO MEET IPC - A - 600, CLASS 2.
- CONSULT TE CONNECTIVITY DATA SHEET DS2195835
- MATERIAL :PI FILM +DOUBLE SIDE ADHESIVE
COAX CABLE DIA. 1.13 I-PEX MHF-4L OR MHF TE APPROVED EQUIVALENT
- ⚠ SILKSCREEN ; WHITE EXPOXY INK
A. TE LOGO P/N
B. WORD REV.,FOLLOWED BY THE LATEST REVISION LETTER AS SHOWN
C. XXXX-SILKSCREEN, 4 DIGITS DATE CODE. FIRST 2 DIGITS FOR WEEK CODE AND THE 2ND TWO DIGITS FOR THE YOUR CODE
OTHERS:SPECIFIC TE SOURCE CODE NUMBER DIGITS AS REQUIRED
- GENERAL TOLERANCE : +/- 0.2mm
- PACKAGING : SINGULATED PARTS TO BE SECURELY BAGE WRAPPED, BAGGED OR VACUUM PACKED IN BULK
- FINISH:
A: SOLDERMASK BOTH SIDE ORANGE
B: ENING PLATING.

	TE PNS	"A" CABLE LENGTH	CONNECTOR	"B" CABLEOD
1	2195835-1	50	MHF TYPE PLUG	1.13
2	2195835-2	100	MHF TYPE PLUG	
3	2195835-3	150	MHF TYPE PLUG	
4	2195835-4	200	MHF TYPE PLUG	
5	2195835-5	50	MHF 4L	
6	2195835-6	100	MHF 4L	
7	2195835-7	150	MHF 4L	
8	2195835-8	200	MHF 4L	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 19DEC2019 DC HSIANG


CHK 06JUN2020 SHIN HOO

APVD 06JUN2020 AMOS CHEAH



DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
FINISH	-

MATERIAL -

19DEC2019

DC HSIANG

06JUN2020

SHIN HOO

06JUN2020

AMOS CHEAH

FPC ANT, MHF/MHF4L, ISM 868/915MHz, HORIZONTAL

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT 0

SIZE A3

CAGE CODE 00779

DRAWING NO C-2195835

RESTRICTED TO -

CUSTOMER DRAWING

SCALE 1:1

SHEET 1 OF 1

REV A1