



POS-NO.	DESCRIPTION	QUANTITY
1	Main insulation part (PBT)	2
2	Half frame ring connector (Al-alloy)	2
3	Bolt with socket head M8x50 (steel, SW6)	2
4	Washer (M10, steel)	2
5	Side wedges (PBT)	2
6	Steel hexagon nut DIN 934, M10	2
7	Adapter part (Brass, tin-plated)	4
8	Protection cap for the tap clamp (PP plastic)	4
9	Teeth element (Brass, tin-plated)	4
10	Grub screw for the tap conductor (Brass, tin-plated SW6)	4
11	Frame for the bow-type tap clamp (Al-alloy)	4

Burr Projection:		DEBUR AND BREAK SHARP EDGES		DO NOT SCALE DRAWING		REVISION: 1	
FORM BOUND MEASURE:		DIMENSION: mm		This Information is confidential and proprietary to Tyco Electronics Corporation and its subsidiaries and affiliates. It may not be disclosed to anyone, other than Tyco Electronics personnel, without written authorization from Tyco Electronics Corporation, Harrisburg, Pennsylvania USA.			
NOT FORM BOUND MEASURE:				DESCRIPTION: HEL-5877; PN:609532-000 RING CONNECTOR with cross-teethed cutting edge Main: 4X120-150SE Branch: 35-120SM, 50-150SE, 10-95RM, 16-120RE			
NAME	SIGNATURE	DATE			DWG NO. C-HEL-5877		A3
DRAWN S. Pollakowski		11.08.2021			SCALE: 1:1		SHEET: 1 OF 1
CHK'D					WEIGHT: 0,9kg		
APPV'D							
 Tyco Electronics Raychem GmbH a TE Connectivity Ltd. company Trachenbergring 85 12249 Berlin (Germany)							