





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	9	TE LOGO AND KEMA LOGO POSITION CHANGED	17SEP2018	RS	OL
	10	SHT 1: DIM 15.21 REF CHANGED TO 15.00 REF	19SEP2018	RS	OL
	11	NEW DESIGN	29AUG2019	RS	MG
	12	DRAWING UPDATE ACC. NEW DESIGN	18JUN2020	SD	MZ

- NOTES:
- CONNECTOR ACCEPTS MULTIPLE WIRES SIZES: SEE TABLE.
 - HOUSING AND BUTTON MATERIAL : POLYCARBONATE
 - IDC CONTACT MATERIAL: TIN PLATED, COPPER ALLOY.
 - LASER MARK LOGO'S: KEMA, PARTNUMBER, TE LOGO, DATE CODE, IP CLASS, UL.
 - WIRE SIZE.
 - FOR WIRE INSULATION DIAMETER RANGE SEE DIMENSION "A" AND "B".

PRELIMINARY PART
NOT RELEASED FOR PRODUCTION
CONTACT ENGINEERING FOR LAST
REVISION BEFORE USING THIS DRAWING
Engineer: S. DERMISEK

A=3.00 B=3.00	GREEN	AWG22/20 (0.33/0.52mm2)	GREEN	AWG22/20 (0.33/0.52mm2)	SEALED	2213920-6	YES
A=3.00 B=3.00	GREEN	AWG22/20 (0.33/0.52mm2)	GREEN	AWG22/20 (0.33/0.52mm2)	STANDARD	2213920-5	ON REQUEST
A=3.50 B=3.00	RED	AWG18/16 (0.75/1.5mm2)	GREEN	AWG22/20 (0.33/0.52mm2)	SEALED	2213920-4	YES
A=3.50 B=3.00	RED	AWG18/16 (0.75/1.5mm2)	GREEN	AWG22/20 (0.33/0.52mm2)	STANDARD	2213920-3	ON REQUEST
A=3.50 B=3.50	RED	AWG18/16 (0.75/1.5mm2)	RED	AWG18/16 (0.75/1.5mm2)	SEALED	2213920-2	YES
A=3.50 B=3.50	RED	AWG18/16 (0.75/1.5mm2)	RED	AWG18/16 (0.75/1.5mm2)	STANDARD	2213920-1	ON REQUEST
HOUSING WIRE ENTRY	COLOR	WIRE SIZE	COLOR	WIRE SIZE	DESCRIPTION	PART NUMBER	AVAILABLE
	BUTTON 1		BUTTON 2				

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 29DEC2016 RAGHAVENDRA.K	 TE Connectivity			
DIMENSIONS:		CHK 29DEC2016 P.POORTER				
mm		APVD 29DEC2016 O.LELIJNSE				
		PRODUCT SPEC 108-133061				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-133061	NAME COOLSPLICE 1 POSITION			
MATERIAL		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-2213920	RESTRICTED TO -
FINISH		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 2	REV 12	

