





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
C2		REVISED PER ECR-24-208483	10APR2024	CJH	TD

- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 8.38±0.076 [.330±.003] CENTERS
- 2 SLOT ACCEPTS 0.36-0.57 [#27-#23 AWG] SINGLE OR DOUBLE COPPER MAGNET WIRE ONLY  
 SLOT ACCEPTS 0.51-0.64 [#24-#22 AWG] SINGLE OR DOUBLE ALUMINUM MAGNET WIRE ONLY  
 SLOT ACCEPTS 0.50-0.51 SINGLE OR 0.45-0.51 DOUBLE ALUMINUM MAGNET WIRE ONLY
- 3 REFER TO DWG 87-1039-3 FOR ADDITIONAL CAVITY INFORMATION (MODIFIED DEPTH)
- 4 0.0010 [.000040] MIN TIN PLATE
- 5 0.45mm SINGLE AL WIRE AND 0.36-0.51mm COPPER WIRE HAS TO BE QUALIFIED -TBD
- 6 WIRE DIAMETER TOLERANCE ALLOW ±0.005mm



4	0.45-0.51	0.36-0.51	0.50-0.51	0.36-0.51	PAPER	2232555-3
4	0.51-0.64	0.36-0.57	0.51-0.64	0.36-0.57	PAPER	2232555-1
FINISH	Al WIRE	Cu WIRE	Al WIRE	Cu WIRE	SPLICE	PART NUMBER
	DOUBLE WIRE RANGE		SINGLE WIRE RANGE			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN R.GRZYBOWSKI 24JUN97	 TE Connectivity TAB, 6.30[.250] CONNECTING, MAG-MATE
	0 PLC ± -	CHK M.S.FEHER 24JUN97	
	1 PLC ± -	APVD N.E.NEFF 24JUN97	
	2 PLC ± 0.25[.010]	PRODUCT SPEC 108-2012	
	3 PLC ± -	APPLICATION SPEC 114-2046	SIZE A2
	4 PLC ± -	ANGLES ± 5°	CAGE CODE 00779
MATERIAL PRE-MILLED BRASS	FINISH SEE TABLE	WEIGHT 0.000000	DRAWING NO C-2232555
		CUSTOMER DRAWING	RESTRICTED TO -
		SCALE 6:1	SHEET 1 of 1
			REV C2