




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 ALL RIGHTS RESERVED.

PROPERTY OF THE TE CONNECTIVITY
 THIS INFORMATION IS CONFIDENTIAL AND PROPERTY TO TYCO ELECTRONICS CORPORATION
 AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES (TE). IT MAY NOT BE DISCLOSED TO
 ANYONE, OTHER THAN TE PERSONNEL, WITHOUT AUTHORIZATION FROM TE (www.TE.com).

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
	A	NEW RELEASE PER ECO-16-000996	140221	SG	JPF		



SOCKET INSERT MARKING SHOWN ABOVE



- MODIFICATION
- KEYING POSITION:
N, A, B, C, D, E
- CONTACT TERMINATION:
Z = CRIMPED CONTACT
A THROUGH Y = EXTENDED CONTACT
- CONTACT FINISH:
P = PIN LOCALIZED GOLD FINISH
S = SOCKET LOCALIZED GOLD FINISH
F = PIN FULL GOLD FINISH
G = SOCKET FULL GOLD FINISH
H = PIN HI REL FINISH
J = SOCKET HI REL FINISH
A = LESS PIN CONTACT
B = LESS SOCKET CONTACT
- SHELL SIZE/INSERT ARRANGMENT
- PLATING/SHELL MATERIAL:
SEE TABLE
- BASIC IDENTIFIER

PART NUMBER (x) ₁	PLATING	SHELL MATERIAL
M	NICKEL	COMPOSITE
J	O.D. CAD	COMPOSITE
F	NICKEL	ALUMINUM
W	O.D. CAD	ALUMINUM
S	NICKEL	STAINLESS STEEL
T	TEFLON NICKEL	ALUMINUM
Z	BLACK ZINC NICKEL	ALUMINUM

SIZE 11 PART NUMBER (x) ₃	POS
CFX26x1108xZN	N
CFX26x1108xZA	A
CFX26x1108xZB	B
CFX26x1108xZC	C
CFX26x1108xZD	D
CFX26x1108xZE	E

- 6. COMPOSITE WEIGHT WITHOUT MODULES AND CABLE: 0.050 POUNDS.
METAL WEIGHT WITHOUT MODULES AND CABLE: 0.078 POUNDS.
PIN MODULE WEIGHT: .005 LBS.
SOCKET MODULE WEIGHT: .011 LBS.

5. MATES WITH CFX20x1108xxx OR CFX24x1108xxx.

4. FINISH: SHELL/BACKSHELL - SEE TABLE.
CONTACTS - SEE PART NUMBER BREAKDOWN.

3. MATERIAL: SHELL & COUPLING RING - SEE TABLE.
BACKSHELL BODY/COUPLING RING - ALUMINUM ALLOY.
CONTACTS - COPPER ALLOY.
RESILIENT INSERTS/BACKSHELL GROMMET - SILICONE ELASTOMER.
PLASTIC INSERTS - THERMOPLASTIC.

2. FOR AVAILABILITY CONSULT FACTORY.

1. ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JPF	140219	STE TE Connectivity	
DIMENSIONS: INCHES		CHK	JPF	160122		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	AR	160122		
0 PLC ±1 1 PLC ±0.1 2 PLC ±0.01 3 PLC ±0.005 4 PLC ±0.0005 ANGLES ±0.5 FINISH		PRODUCT SPEC				
MATERIAL		APPLICATION SPEC			NAME	CONNECTOR, PLUG THREADED COUPLING 1108 ARRANGEMENT
		WEIGHT			SIZE	A2
		CUSTOMER DRAWING			CAGE CODE	11139
					DRAWING NO	CFX26x1108xxx
					RESTRICTED TO	-
					SCALE	3.000
					SHEET	1 OF 1
					REV	A