

4

3

2

1

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

2018

© COPYRIGHT 2018 BY - TE CONNECTIVITY

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER PCN E-18-015129	13DEC2018	SS	DM
	A2	DRAWING UPDATED	12MAR2024	RK	CB

TE INTERNAL PN	DEUTSCH PN
DTHD06-1-4S	DTHD06-1-4S

WIRE INSULATION DIA		
CONTACT SIZE	MINIMUM O.D.	MAXIMUM O.D.
4	.261 [6.63]	.420 [10.67]

4 DATE CODE: MONTH IS REPRESENTED BY SEQUENTIAL ALPHA CHARACTERS. EX: A = JANUARY. YEAR IS REPRESENTED BY LAST NUMERIC DIGIT. EX: 7 = 2007.

3 MATERIAL: PLUG: PEI (BLACK); INTERFACE SEAL: VMQ (RED-ORANGE)

2. THIS PLUG MATES WITH DTHD04-1-4P-XXXX RECEPTACLE. (XXXX = ALL MODIFICATIONS)

1. FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTIC SEE CUSTOMER DRAWING 0425-015-0000.

NOTES: UNLESS OTHERWISE SPECIFIED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V. TONSA 09JUN2004														
DIMENSIONS: INCHES [mm]		CHK D. MEYER 10JUN2004														
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. MEYER 21JUN2004	NAME PLUG #4 HD CONTACT DTHD SERIES COLOR: BLACK													
<table border="1"> <tr> <td>0 PLC</td> <td>±-</td> </tr> <tr> <td>1 PLC</td> <td>±-</td> </tr> <tr> <td>2 PLC</td> <td>±-</td> </tr> <tr> <td>3 PLC</td> <td>±.025 [0.64]</td> </tr> <tr> <td>4 PLC</td> <td>±-</td> </tr> <tr> <td>ANGLES</td> <td>±0°30'0"</td> </tr> </table>		0 PLC	±-	1 PLC	±-	2 PLC	±-	3 PLC	±.025 [0.64]	4 PLC	±-	ANGLES	±0°30'0"	PRODUCT SPEC 108-151020	SIZE A3	
0 PLC	±-															
1 PLC	±-															
2 PLC	±-															
3 PLC	±.025 [0.64]															
4 PLC	±-															
ANGLES	±0°30'0"															
MATERIAL 3		APPLICATION SPEC 114-151020	CAGE CODE 4AFU8	DRAWING NO DTHD06-1-4S												
FINISH -		WEIGHT 11 g	RESTRICTED TO													
		CUSTOMER DRAWING	SCALE 3:1	SHEET 1 OF 1												
			REV A2													

1470-19 (3/13)