



WARNING - THIS DOCUMENT CONTAINS TECHNOLOGY WHOSE EXPORT IS RESTRICTED BY THE EXPORT ADMINISTRATION REGULATIONS ("EAR") PURSUANT TO 15 C.F.R. PARTS 730-774. VIOLATIONS OF THE EAR ARE SUBJECT TO SEVERE CRIMINAL PENALTIES UNDER THE EXPORT CONTROL REFORM ACT, AS AMENDED (TITLE 50, U.S.C., SEC. 4801, ET SEQ.).

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	J	RELEASE PER ECN-24-272876	JUN2024	RTF JG



RECOMMENDED STRIP LENGTH

INNER FERRULE	BRASS PER ASTM B16 OR B36	SILVER PLATE PER ASTM B700
DIELECTRICS	PTFE FLOUROCARBON PER ASTM-D-1457	N/A
SHELL	BRASS PER ASTM B16	SILVER PLATE PER ASTM B700
PIN	BRASS PER ASTM B16	GOLD PLATE PER ASTM B488 OVER NICKEL PLATE PER SAE-AMS-QQ-N-290
WASHER	PHOSPHOR BRONZE PER ASTM B139	N/A
COUPLING NUT	BRASS PER ASTM B16	SILVER PLATE PER ASTM B700
GASKET	SILICONE RUBBER PER A-A-59588	N/A
OUTER CONTACT	PHOSPHOR BRONZE PER ASTM B139	SILVER PLATE PER ASTM B700
FEMALE CONTACT	BeCu PER ASTM B196	GOLD PLATE PER ASTM B488
CONTACT CRIMP BARREL	BRASS PER ASTM B16	GOLD PLATE PER ASTM B488
CRIMP FERRULE	COPPER OR BRASS ALLOY ROCKWELL B45 MAX	SILVER PLATE PER ASTM B700
COMPONENT	MATERIAL	FINISH

NOTES:

1. USE CRIMPING TOOL 220015-1
2. SEE INSTRUCTION SHEET 408-2028-5

RG-214/U	00779M39012/05 B 0003 AMP & DATE CODE (YY-WW)	225014-3
CABLE SIZE	STAMPING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. FRAZIER 17 JUN 2024	TE Connectivity	
DIMENSIONS: mm		CHK J. GUNDERMANN 17 JUN 2024		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. WILSON 17 JUN 2024	NAME PLUG, RIGHT ANGLE, SERIES N	
0 PLC ± 1 PLC ± 2 PLC ±0.41 [.016] 3 PLC ± 4 PLC ± ANGLES ± FINISH -		PRODUCT SPEC 108-12019	RESTRICTED TO -	
MATERIAL -		APPLICATION SPEC -	SIZE A2	CAGE CODE 00779
		WEIGHT -	DRAWING NO C-225014	
		SCALE 2:1		SHEET 1 OF 1
				REV J