



LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
			A1	PER ECR-15-015943	30OCT2015	N.P	X.X	
			A2	PER ECR-20-005213	08APR2020	F.Y	C.W	
			A3	PER ECR-21-001469	04FEB2021	F.Y	C.W	
			B	PER ECR-21-102523	21MAY2021	G.W	C.W	




RECOMMENDED PANEL HOLE SIZE
4.5mm MAX PANEL THICKNESS

SPCIFICATION:


1. MI2 8P RECEPTACLE REAR MOUNT SHIELDED TYPE.
2. RATED VOLTAGE:48V, RATED CURRENT: 0.5A.
3. CONTACT RESISTANT: 5 mOhm MAX.
4. INSULATION WITHSTAND: 100 MOhm MIN.
5. PROTECTION: IP67.
6. TEMPERATURE RANGE: -25°~+85°.
7. TRANSMISSION CHARACTERISTICS: CAT6a.
8. PACKAGE:40PCS/TRAY,10TRAYS/BOX(TOTAL 400PCS).
9. SUITABLE WIRE RATING: 22~28AWG

规格:

1. M12 8针 板后屏蔽型母座.
2. 额定电压:48V, 额定电流:0.5A
3. 接触阻抗:5 mOhm MAX.,
4. 绝缘阻抗:100MOhm MIN.
5. 保护等级:IP67
6. 温度范围:-25°~+85°.
7. 传输特性:CAT6a
8. 包装规范:40PCS/TRAY,10TRAYS/箱(共400pcs产品)
9. 适用导线规格:22~28AWG



ITEM	DESCRIPTION	MATERIAL	FINISH/COLOR
1	INSERT HOUSING	PA	BLACK
2	HEXAGONAL SHELL	ZINC ALUMINUM ALLOY	NICKEL OVER COPPER
3	SOCKET CONTACT	COPPER ALLOY	GOLD OVER NICKEL
4	SEALER RING	LSR	BLACK
5	HEXAGONAL NUT	COPPER ALLOY	NICKEL OVERALL
6	SEALER RING	LSR	BLACK
7	CROSS SHIELDED	ZINC ALUMINUM ALLOY	NICKEL OVER COPPER TIN OVER NICKEL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FENCER YU	24JUN2015	 TE Connectivity					
		CHK KOBBY ZHAO	24JUN2015						
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD XIANG YU	24JUN2015	NAME REAR PANEL MOUNT SOLDER CONNECTOR M12 X-CODE			
mm		0 PLC				PRODUCT SPEC 108-137008 APPLICATION SPEC 114-137008 WEIGHT -			
		1 PLC		±0.3					
		2 PLC		±0.20					
		3 PLC		±0.20					
		4 PLC		±0.20					
		ANGLES		±0.20					
		FINISH		-					
		-		-					
		-		-					
		-		-					
MATERIAL				SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
-				A1	00779	C=2271195	-		
Customer Drawing				SCALE	6:1	SHEET	1 OF 1	REV	B