


P	LTR	DESCRIPTION	DATE	DWN	APVD
1		NEW DRAWING	24JUL2020	KR	AMO





NOTES :

- DIMENSIONS IN mm. a = AS SUPPLIED, b = AFTER FREE RECOVERY
- STANDARD LENGTHS P: 1000 mm and 1500 mm. OTHER CUT LENGTHS AVAILABLE UNDER REQUEST
- MAXIMUM LONGITUDINAL CHANGE AFTER FREE RECOVERY: +0%/-10%
- STANDARD CUT LENGTH TOLERANCES:
 - ± 6 mm (P ≤ 200)
 - ± 9 mm (P > 200)
 - ± 13 mm (P > 300)
 - ± 15 mm (P > 450)
 - 0/+40 mm (P > 1000)
- STANDARD PRINTING /S (COATED): LOGO, XCSM, PRODUCT SIZE, BATCH NUMBER

PRODUCT SIZE	APPLICATION RANGE		DIMENSIONS		
			H		W
	MIN	MAX	"a" MIN	"b" MAX	"b" MIN
XCSM 30/8	9	27	30	8	3.0
XCSM 44/12	13	39.5	44	12	3.0
XCSM 55/18	20	49.5	55	18	3.0
XCSM 85/22	21	76.5	85	22	2.7
XCSM 115/30	29	104	115	30	3.1
XCSM 130/41	39	117	130	41	3.1
XCSM 160/55	61	144	160	55	3.2
XCSM 178/60	66	150	178	60	3.2



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA K. 24JUL2020	 TE Connectivity		
DIMENSIONS: mm		CHK AMO 24JUL2020			
		APVD AMO 24JUL2020	NAME XCSM HEAT SHRINK TUBING		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	SIZE		
0 PLC ± -		—	CAGE CODE		
1 PLC ± -		APPLICATION SPEC	DRAWING NO		
2 PLC ± -		—	RESTRICTED TO		
3 PLC ± -		—	A3 00779		
4 PLC ± -		—	G-EPD-202-311928-01		
ANGLES ± -		WEIGHT	—		
MATERIAL		FINISH	SCALE		
—		—	NTS		
		CUSTOMER DRAWING		SHEET	REV
				1 OF 1	1