

4

3

2

1



© - TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
1		NEW DRAWING	31AUG2020	KR	AMO

D

D



NOTES

- DIMENSIONS IN mm. a = AS SUPPLIED, b = AFTER FREE RECOVERY
- COATING CODE: /239.
- MAXIMUM LONGITUDINAL CHANGE AFTER FREE RECOVERY: -10%/+10%  
STANDARD CUT LENGTH TOLERANCES:  
± 3% (P > 250)  
± 15 mm (P > 500)
- STANDARD PRINTING: LOGO, PRODUCT SIZE, BATCH NUMBER

C

C

PRODUCT SIZE	APPLICATION RANGE (MM)		H		R		S	W		P
	MIN.	MAX.	a min	b max	a min	b max	a min	a min	b min	a min
MRS-12-10	25	40	50	23	159	72	20	0.8	1.8	255
MRS-12-24	25	40	50	23	159	72	20	0.8	1.8	610
MRS-34-24	40	58	73	38	230	119	20	0.5	1.8	610
MRS-34-30	40	58	73	38	230	119	20	0.5	1.8	760
MRS-56-30	58	89	100	51	320	161	20	0.5	1.8	760
MRSM-50/23	25	40	50	23	159	72	20	0.8	1.8	250/600
MRSM-73/38	40	58	73	38	230	119	20	0.5	1.8	300/600/750
MRSM-100/51	58	89	100	51	320	161	20	0.5	1.8	600/750



B

B

A

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	31AUG2020	TE Connectivity	
		CHK	31AUG2020		
DIMENSIONS: mm		APVD	31AUG2020	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		MRS/MRSM FLAME RETARDANT WRAPAROUND SLEEVES	
0 PLC ± -		APPLICATION SPEC		SIZE	
1 PLC ± -		WEIGHT		CAGE CODE	
2 PLC ± -		CUSTOMER DRAWING		DRAWING NO	
3 PLC ± -		SCALE		RESTRICTED TO	
4 PLC ± -		NTS		A3	
ANGLES ± -		SHEET		00779	
FINISH		1 of 1		C-EPD-202-32016-01	
-		REV		-	
-		1		-	