



P	LTR	DESCRIPTION	DATE	DWN	APVD
1		NEW DRAWING	31AUG2020	KR	SH

TYPE
CSJH
Hybrid straight joint



Material	L* approx (mm)	Material	L* approx (mm)
CSJH-12B1/1XU-1XU CSJH-12B1/1XU-1XU-M	650	CSJH-24E/1XU-1XU CSJH-24E/1XU-1XU-M	1000
CSJH-12B/1XU-1XU CSJH-12B/1XU-1XU-M	700	CSJH-24F/1XU-1XU CSJH-24F/1XU-1XU-M	1000
CSJH-12C/1XU-1XU CSJH-12C/1XU-1XU-M	700	CSJH-36D/1XU-1XU CSJH-36D/1XU-1XU-M	800
CSJH-12D/1XU-1XU CSJH-12D/1XU-1XU-M	800	CSJH-36E/1XU-1XU CSJH-36E/1XU-1XU-M	1000
CSJH-12E/1XU-1XU CSJH-12E/1XU-1XU-M	1000	CSJH-36F/1XU-1XU CSJH-36F/1XU-1XU-M	1000
CSJH-12F/1XU-1XU CSJH-12F/1XU-1XU-M	1000		
CSJH-24B/1XU-1XU CSJH-24B/1XU-1XU-M	700		
CSJH-24C/1XU-1XU CSJH-24C/1XU-1XU-M	700		
CSJH-24D/1XU-1XU CSJH-24D/1XU-1XU-M	800		

CSJR
Cold applied straight joint with Rayvolve re-jacketing



Material	L* approx (mm)
CSJR-24B/1XU-1XU CSJR-24B/1XU-1XU-M	600
CSJR-24C/1XU-1XU CSJR-24C/1XU-1XU-M	600
CSJR-24D/1XU-1XU CSJR-24D/1XU-1XU-M	750
CSJR-36D/1XU-1XU CSJR-36D/1XU-1XU-M	750
CSJR-36E/1XU-1XU CSJR-36E/1XU-1XU-M	800

*based on the BSM mechanical connectors based on DIN VDE 0276 HD 620 A (2004)
Variations possible depending on cable dimensions and cable connector configuration

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA K 31AUG2020	TE Connectivity Ltd.	
DIMENSIONS: mm		CHK SEJLA HELJO 31AUG2020		
		APVD SEJLA HELJO 31AUG2020	NAME MV cold applied joints CSJH/CSJR joints	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	SIZE A3	
0 PLC ± -		APPLICATION SPEC	CAGE CODE 00779	DRAWING NO EPD-204-2261-00
1 PLC ± -		—	RESTRICTED TO —	
2 PLC ± -		WEIGHT	SCALE NTS	
3 PLC ± -		CUSTOMER DRAWING	SHEET 1 of 1	
4 PLC ± -		FINISH	REV 1	
ANGLES ± -				
MATERIAL				