

12

signal max. 5 A\* 63 V (AC/DC) 1500 V

500

3 III

Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

2000 m

FKM

-20 °C to 130 °C

Ø 6,5 mm to Ø 8.5 mm when connected IP 66/67

zinc diecast / plastic coated PBT, PA, UL 94/V0

brass / nickel plated

**Technical Data** 

rated voltage rated insulation voltage (L-L)

number of pins temperature range

clamping range

protection type **Electrical Data** 

rated current

mating cycles

Material

housina insulation insert seals

clamp ring

pollution degree over voltage category

max. height for operation

## 615 Plug

12-pin **EMC - Shielding** 

## E ST A 002 NN 00 32 0001 000 E S A 002 N 00 32 0001 000



**Contact Arrangement** mating view



Contacts (not part of product contents)

Tools (not part of product contents)

© 2018 TE Connectivity


TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without protice. Consult TE for the

notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications. TE Connectivity Industrial GmbH Bernrieder Straße 15 94559 Niederwinkling, Deutschland Tel.: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mali: intercontec@te.com Web: www.intercontec.biz

issue: 03.09.2018





**Main Dimensions** Plug

\*for max. wire cross-section pay attention to the cross-section of used contacts