

REVISIONS				
P	LTN	DESCRIPTION	DATE	APP'D
A		RELEASED PER ECO-19-001811	05FEB2019	DCB AT
B		REV PER ECO-21-003080	16OCT2021	LN DH

- 1 HOUSING: LCP, UL94V0, COLOR: BLACK.
CONTACT: PHOSPHOR BRONZE.
POST: BRASS WIRE
- 2 PLATED THROUGH HOLE PER TE SPEC 114-13056, FIGURE 4 OR 114-163004, FIGURE 10.
- 3 PLATED THRU HOLE SPECIFICATION:
DRILLED HOLE: $\varnothing 0.40 \pm 0.02$
0.025-0.050 THICK COPPER PLATING (MAX HARDNESS 150 KNOOP)
FINISH OPTIONS:
0.0038-0.0124 HOT AIR SOLDER LEVELING (HASL) TIN-LEAD (SnPb)
0.0005-0.004 IMMERSION TIN (Sn)
0.0002-0.0005 ORGANIC SOLDERABILITY PRESERVATIVE (OSP)
0.0001-0.0005 IMMERSION SILVER (Ag)
0.0001-0.0005 IMMERSION GOLD OVER 0.00127-0.0076 NICKEL (ENIG)
FINISH HOLE DIAMETER AFTER PLATING = $\varnothing 0.31$ REF
- 4 CONTACT: 1.27 μ m MIN GOLD IN PAD CONTACT AREA
1.27 μ m MIN TIN-LEAD (93/7) ON PCB TAILOVER 1.27 μ m MIN. NICKEL ALL OVER
POST: 1.27 μ m MIN NICKEL PLATED.
- 5 SEE TABLE 1 FOR INTERCONNECTIONS TO BACKPLANE CONNECTOR.
- 6 CONTACT: 1.27 μ m MIN GOLD IN PAD CONTACT AREA,
1.27 μ m MIN TIN ON PCB TAIL OVER 1.27 μ m MIN.
NICKEL OVER ALL.
POST: 1.27 μ m MIN NICKEL PLATED.
- 7 CONTACT: 1.27 μ m MIN GOLD IN PAD CONTACT AREA
1.27 μ m MIN TIN-LEAD (60/40) ON PCB TAILOVER 1.27 μ m MIN. NICKEL ALL OVER
POST: 1.27 μ m MIN NICKEL PLATED.

TABLE 1
INTERCONNECTIONS WITH BACKPLANE CONNECTOR 2313238

TYPICAL INTERCONNECTIONS FOR COLUMN (WAFER): 7, 9, 11, 13, 15		
CONTACT USAGE	DAUGHTERCARD CONNECTOR PIN	BACKPLANE CONNECTOR PIN
SIGNAL PAIR	ax	ax
	bx	bx
SIGNAL PAIR	dx	ex
	ex	fx
SIGNAL	gx	ix
GROUPS	cx, fx, (ALL COMMONED)	cx, dx, gx, hx

TYPICAL INTERCONNECTIONS FOR COLUMN (WAFER): 8, 10, 12, 14, 16		
CONTACT USAGE	DAUGHTERCARD CONNECTOR PIN	BACKPLANE CONNECTOR PIN
SIGNAL PAIR	bx	cx
	cx	dx
SIGNAL PAIR	ex	gx
	fx	hx
GROUPS	ax, dx, gx (ALL COMMONED)	ax, bx, ex, fx, ix

TYPICAL INTERCONNECTIONS FOR COLUMN (WAFER): 4, 5, 6		
CONTACT USAGE	DAUGHTERCARD CONNECTOR PIN	BACKPLANE CONNECTOR PIN
SIGNAL	ax	bx
SIGNAL	bx	cx
SIGNAL	dx	ex
SIGNAL	fx	gx
SIGNAL	gx	hx
GROUPS	cx, ex (ALL COMMONED)	ax, dx, fx, ix

TYPICAL INTERCONNECTIONS FOR COLUMN (WAFER): 1, 2, 3		
CONTACT USAGE	DAUGHTERCARD CONNECTOR PIN	BACKPLANE CONNECTOR PIN
POWER	ax, bx, cx	ax, bx, cx, dx
POWER	ex, fx, gx	fx, gx, hx, ix
NOT CONNECTED	dx	ex

NOTE: "x" DESIGNATES THE COLUMN NUMBER

1	2313237-3
6	2313237-2
4	2313237-1
PLATING	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.




OWN: A. MILLER 10JUL2017
CHK: A. TSANG 10JUL2017
APP'D: -

DIMENSIONS: mm
TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± 0.13
1 PLC ± 0.5
2 PLC ± 0.13
3 PLC ± 0.13
4 PLC ± 0.13
ANGLES: $\pm 0.1^\circ$
FINISH: SEE TABLE

PRODUCT SPEC: 108-2072-3
APPLICATION SPEC: 114-163004
WEIGHT: 10.33g
CUSTOMER DRAWING

NAME: RIGHT-ANGLE PLUG ASSY, 7 ROW, CENTER, DIFFERENTIAL, SINGLE-ENDED AND POWER VPX, MULTIGIG RT 3
SIZE: 10.33g
CAGE CODE: 114-163004
DRAWING NO: 100779
RESTRICTED TO: A

TE Connectivity
SCALE: 6:1 SHEET 1 OF 1 REV B



16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1
	P		P		P		P		P		P		P		P
3	3	3	3	3	3	3	3	3	2	2	2	2	2	2	2
3	3	3	3	3	3	3	3	3	2	2	2	2	2	2	2
3	3	3	3	3	3	3	3	3	2	2	2	2	2	2	2
3	3	3	3	3	3	3	3	3	2	2	2	2	2	2	2
3	3	3	3	3	3	3	3	3	2	2	2	2	2	2	2
3	3	3	3	3	3	3	3	3	2	2	2	2	2	2	2
3	3	3	3	3	3	3	3	3	2	2	2	2	2	2	2

2 = RT2 CONTACT (SEE NOTE 2)
3 = RT3 CONTACT (SEE NOTE 3)
P = POST

