



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - TE Connectivity ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN APVD
B		REVISED	19MAR2018	H.O E.I

D

D



RECOMMENDED PC BOARD HOLE PATTERN (TOLERANCE:±0.05)
 PC BOARD THICKNESS:1.6±0.3
 (CONNECTOR MOUNT SIDE)

1. MATERIAL:HOUSING:GRASS FILED THERMO PLASTIC,POLYAMIDE(94V-0),BLACK
 TAB CONTACT:COPPER ALLOY
 RETENTION LEG:BRASS
2. FINISH(CONTACT AREA):0.38μmMIN GOLD PLATEDING OVER NICKEL PLATING
3. FINISH(RETENTION LEG , CONTACT TAIL):TIN PLATED OVER NICKEL PLATING
4. NET WEIGHT:2.76g

WITH	X	1-2322866-1
W/O	Y	2322866-2
SEQ	KEY	PART No.

C


C

B

B

A

A



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 10% ± 0.3 1 PLC ± 20% ± 0.35 2 PLC ± 20% ± 0.4 3 PLC ± - 4 PLC ANGLES ± 3'	DWN H.OSABE 11DEC2017 CHK T.SHIMOYASU 11DEC2017 APVD E.IKEMATSU 11DEC2017		
MATERIAL SEE NOTES	FINISH SEE NOTES	PRODUCT SPEC 108-5619	DOUBLE ROW HEADER ASSY 8P H-TYPE DYNAMIC D-2100D	
		APPLICATION SPEC -	SIZE A3	CAGE CODE 00779
		WEIGHT 0.00	DRAWING NO C=2322866	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 2
			REV B	

4

3



2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - TE Connectivity ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-

1-2322866-1; AS SHOWN
 SEQUENTIAL TYPE




SECT A-A

		CIRCUIT NO.			
		1	2	3	4
LINE	B	③ Signal	① Ground	③ Signal	③ Signal
	A	④ Signal	② Ground	④ Signal	④ Signal

POINT OF SEQUENTIAL
1-2322866-1
 (KEYING X)

NOTES

- MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC, POLYAMIDE(94V-0), COLOR: BLACK
 TAB CONTACT: COPPER ALLOY
 RETENTION LEG: BRASS
- FINISH (CONTACT AREA): 0.38 μm MIN GOLD PLATING OVER Ni PLATING
 FINISH (RETENTION LEG): TIN PLATED (CONTACT TAIL) OVER NICKEL
- NET WEIGHT: 2.72g



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.OSABE 27OCT2017		
		CHK T.SHIMOYASU 11DEC2017		
DIMENSIONS: mm		APVD E.IKEMATSU 11DEC2017	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	DOUBLE ROW HEADER ASSY 8P H-TYPE	
0 PLC ± .10 ± 0.3		APPLICATION SPEC	DYNAMIC D-2100D	
1 PLC ± .15 ± 0.35		WEIGHT	-	
2 PLC ± .20 ± 0.4		SIZE	CAGE CODE	DRAWING NO
3 PLC ± .25 ± 0.4		A3	00779	C=2322866
4 PLC ± .30 ± 0.4		RESTRICTED TO		
4 ANGLES ± 3'		SCALE		SHEET
MATERIAL SEE NOTES		CUSTOMER DRAWING		4:1 2 OF 2
FINISH SEE NOTES		REV		B