



REVISIONS				
P.	LT#	DESCRIPTION	DATE	DWN APVD
3		REVISED NOTES 4 AND 5 PER ECO-20-013269	21SEP2020	REH MS



- SEE SHEET 2 FOR WIRING SCHEMATIC.
- ALL MATERIALS, COMPONENTS AND PROCESSES SHALL COMPLY WITH TEC-138-702. (CONTAIN NO BANNED OR RESTRICTED SUBSTANCES).
- NO REACH SvHC SHALL BE CONTAINED ABOVE THE THRESHOLD AS DEFINED IN REACH SvHC COMPLIANCE DEFINITION IN ANNEX A OF TEC-138-702.
- CABLE ASSEMBLIES ARE 100% TESTED FOR OPENS, SHORTS, HI-POT, AND PROPER EEPROM PROGRAM.

△ LABEL INFORMATION: -1 SHOWN.




OSFP - (8) SFP
 2324443-1
 0.5M 30AWG
 P P P P P L Y Y W W X X X
 SERIAL NUMBER BARCODE
 COUNTRY OF ORIGIN
 MADE IN ...

- ← TE LOGO
- ← TE PART NUMBER
- ← CONFIGURATION
- ← SERIAL NUMBER

THIS PRODUCT HAS NOT COMPLETED VALIDATION AND QUALIFICATION TESTING

PRELIMINARY NOT RELEASED FOR PRODUCTION

2M 30AWG	2000±30	2324443-4
1.5M 30AWG	1500±25	2324443-3
1M 30AWG	1000±20	2324443-2
0.5M 30AWG	500±20	2324443-1
CONFIGURATION	L	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. SMITH 06JUN2018	 TE Connectivity
DIMENSIONS: mm		CHK K. STAUFFER 06JUN2018	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K. STAUFFER 06JUN2018	NAME CABLE ASSEMBLY, 30 AWG OSFP TO (8) SFP56
0 PLC ±		PRODUCT SPEC	SIZE CAGE CODE DRAWING NO
1 PLC ±		APPLICATION SPEC	A100779C=2324443
2 PLC ±		WEIGHT	RESTRICTED TO
3 PLC ±		RESTRICTED CUSTOMER	SCALE 5:1 SHEET 1 OF 2 REV 3
4 PLC ±			
ANGLES ±			
FINISH ±			

REVISIONS				
P.	LTN	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-

P1 (OSFP)			P2 (SFP56)	
GND				GND
TX1+	59	↔	13	RX1+
TX1-	58	↔	12	RX1-
GND				GND
RX1+	29	↔	18	TX1+
RX1-	28	↔	19	TX1-
GND				GND

P1 (OSFP)			P3 (SFP56)	
GND				GND
TX2+	2	↔	13	RX1+
TX2-	3	↔	12	RX1-
GND				GND
RX2+	32	↔	18	TX1+
RX2-	33	↔	19	TX1-
GND				GND

P1 (OSFP)			P4 (SFP56)	
GND				GND
TX3+	56	↔	13	RX1+
TX3-	55	↔	12	RX1-
GND				GND
RX3+	26	↔	18	TX1+
RX3-	25	↔	19	TX1-
GND				GND

P1 (OSFP)			P5 (SFP56)	
GND				GND
TX4+	5	↔	13	RX1+
TX4-	6	↔	12	RX1-
GND				GND
RX4+	35	↔	18	TX1+
RX4-	36	↔	19	TX1-
GND				GND

P1 (OSFP)			P6 (SFP56)	
GND				GND
TX5+	53	↔	13	RX1+
TX5-	52	↔	12	RX1-
GND				GND
RX5+	23	↔	18	TX1+
RX5-	22	↔	19	TX1-
GND				GND

P1 (OSFP)			P7 (SFP56)	
GND				GND
TX6+	8	↔	13	RX1+
TX6-	9	↔	12	RX1-
GND				GND
RX6+	38	↔	18	TX1+
RX6-	39	↔	19	TX1-
GND				GND



P1 (OSFP)			P8 (SFP56)	
GND				GND
TX7+	50	↔	13	RX1+
TX7-	49	↔	12	RX1-
GND				GND
RX7+	20	↔	18	TX1+
RX7-	19	↔	19	TX1-
GND				GND

P1 (OSFP)			P9 (SFP56)	
GND				GND
TX8+	11	↔	13	RX1+
TX8-	12	↔	12	RX1-
GND				GND
RX8+	41	↔	18	TX1+
RX8-	42	↔	19	TX1-
GND				GND

WIRING PATTERN

THIS PRODUCT HAS NOT COMPLETED VALIDATION AND QUALIFICATION TESTING

PRELIMINARY NOT RELEASED FOR PRODUCTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. SMITH 06JUN2018 CHK K. STAUFFER 06JUN2018 APVD K. STAUFFER 06JUN2018	 TE Connectivity
DIMENSIONS: mm 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	NAME CABLE ASSEMBLY, 30 AWG OSFP TO (8) SFP56 PRODUCT SPEC - APPLICATION SPEC - SIZE CAGE CODE DRAWING NO. A100779C=2324443 WEIGHT - RESTRICTED CUSTOMER	
MATERIAL - FINISH -		RESTRICTED TO	SCALE 5:1 SHEET 2 OF 2 REV 3