



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
3		REVISED NOTES 4 AND 5 PER ECO-20-013264	01OCT2020	REH	MS



1. SEE SHEET 2 FOR WIRING SCHEMATIC.
2. ALL MATERIALS, COMPONENTS AND PROCESSES SHALL COMPLY WITH TEC-138-702. (CONTAIN NO BANNED OR RESTRICTED SUBSTANCES).
3. NO REACH SvHC SHALL BE CONTAINED ABOVE THE THRESHOLD AS DEFINED IN REACH SvHC COMPLIANCE DEFINITION IN ANNEX A OF TEC-138-702.
4. CABLE ASSEMBLIES ARE 100% TESTED FOR OPENS, SHORTS, HI-POT, AND PROPER EEPROM PROGRAM.
- △ 5 LABEL INFORMATION: -1 SHOWN.



OSFP - (2) QSFP
2335033-1
2M 26AWG
PPPPPLYWWXXX
MADE IN ...

—TE LOGO

—TE PART NUMBER

—CONFIGURATION

—SERIAL NUMBER

SERIAL NUMBER BARCODE

COUNTRY OF ORIGIN

THIS PRODUCT HAS NOT COMPLETED VALIDATION AND QUALIFICATION TESTING

PRELIMINARY NOT RELEASED FOR PRODUCTION

3M 26AWG	3000±30	2335033-3
2.5M 26AWG	2500±30	2335033-2
2M 26AWG	2000±30	2335033-1
CONFIGURATION	L	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MATTHEWS 18APR2018	 TE Connectivity		
		CHK K. STAUFFER 18APR2018			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH	APVD K. STAUFFER 18APR2018	NAME CABLE ASSEMBLY, OSFP TO (2) QSFP		
		PRODUCT SPEC -	SIZE CAGE CODE DRAWING NO		
		APPLICATION SPEC -	A100779C=2335033		
		WEIGHT -	RESTRICTED TO		
MATERIAL		CUSTOMER DRAWING	SCALE 5:1	SHEET 1 OF 2	REV 3

P1 (OSFP)			P2 (QSFP)	
GND				GND
TX2+	2	↔	22	RX2+
TX2-	3	↔	21	RX2-
GND				GND
TX4+	5	↔	25	RX4+
TX4-	6	↔	24	RX4-
GND				GND
GND				GND
RX3-	25	↔	34	TX3-
RX3+	26	↔	33	TX3+
GND				GND
RX1-	28	↔	37	TX1-
RX1+	29	↔	36	TX1+
GND				GND
GND				GND
RX2+	32	↔	3	TX2+
RX2-	33	↔	2	TX2-
GND				GND
RX4+	35	↔	6	TX4+
RX4-	36	↔	5	TX4-
GND				GND
GND				GND
TX3-	55	↔	15	RX3-
TX3+	56	↔	14	RX3+
GND				GND
TX1-	58	↔	18	RX1-
TX1+	59	↔	17	RX1+
GND				GND

P1 (OSFP)			P3 (QSFP)	
GND				GND
TX6+	8	↔	22	RX2+
TX6-	9	↔	21	RX2-
GND				GND
TX8+	11	↔	25	RX4+
TX8-	12	↔	24	RX4-
GND				GND
GND				GND
RX7-	19	↔	34	TX3-
RX7+	20	↔	33	TX3+
GND				GND
RX5-	22	↔	37	TX1-
RX5+	23	↔	36	TX1+
GND				GND
GND				GND
RX6+	38	↔	3	TX2+
RX6-	39	↔	2	TX2-
GND				GND
RX8+	41	↔	6	TX4+
RX8-	42	↔	5	TX4-
GND				GND
GND				GND
TX7-	49	↔	15	RX3-
TX7+	50	↔	14	RX3+
GND				GND
TX5-	52	↔	18	RX1-
TX5+	53	↔	17	RX1+
GND				GND

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

THIS PRODUCT HAS NOT COMPLETED VALIDATION AND QUALIFICATION TESTING

PRELIMINARY
NOT RELEASED FOR PRODUCTION

WIRING PATTERN

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

FINISH
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH ±

DWN
B. MATTHEWS
CHK
K. STAUFFER
APVD
K. STAUFFER

18APR2018
18APR2018
18APR2018

PRODUCT SPEC
APPLICATION SPEC
WEIGHT
CUSTOMER DRAWING

NAME
CABLE ASSEMBLY,
OSFP TO (2) QSFP

SIZE
A

CAGE CODE
00779

DRAWING NO
2335033

RESTRICTED TO

SCALE
5:1

SHEET
2

OF
2

REV
3