

REV. B
DCO 301387

BLUE BEAD


TOLERANCES $\pm .010$ " - UNLESS OTHERWISE SPECIFIED

COIL: @ 25°C
 RESISTANCE _____ 290 OHMS $\pm 10\%$
 NOMINAL VOLTAGE _____ 28 VDC
 MUST OPERATE _____ 13.5 VDC MAX.
 _____ COIL TRANSIENT SUPPRESSION: 42 VDC MAX.
 MUST RELEASE _____ 5.5 VDC MAX., 2.3 VDC MIN.

ENVIRONMENT:
 VIBRATION _____ 10 _____ Hz TO _____ 3000 _____ Hz @ _____ 30 _____ g's
 SHOCK _____ 200 _____ g's _____ 6 _____ MS. DURATION
 TEMPERATURE _____ -70 _____ °C TO _____ +125 _____ °C

NOTES: _____ OPERATE, RELEASE 15 MS MAX.
 _____ CONTACT STABILIZATION 2.5 MS MAX.
 _____ CONTACT BOUNCE 1 MS MAX.
 _____ CONTACT BREAK BOUNCE 0.1 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: _____ LOW LEVEL
 _____ 10 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE
 _____ 100,000 OPERATIONS

DR. R.F. 21APR2011 CK. M.B. 26APR2011



CUST. _____ QPL
 CUST. NO. _____ M83536/16-022L REV. _____

TE NUMBER
 2-1617754-0

CII PART NUMBER
 FCA-410-1622L