



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	3	RELEASED AS PER ECO-17-009529	03JUL2017	KH	MP

a) Part as supplied.



b) Part after unrestricted recovery.



NOTES:

Raychem Connector Code: 54
 Connector Series: MIL-C-5015 (MS3400)
 Adaptor Series: 203M0**-19-B**-K-NS (Olive Drab)
 Aluminium Alloy to BS1474 HE30TF, FC1 or 6262
 Cadmium per QQ-P-416, Type II, Class 3
 Over appropriate under plate,
 Per MIL-C-85049 (500 hour salt spray)

Moulded Part Material: -25C (Black); Elastomer/Silver Composites, Fluid Resistant

Kits to include cleaning tissue, 1 piece 100 grit emery cloth & packing piece.
 Kit to be used in conjunction with installation guide for straight assemblies.

Dimensions in mm [inches for reference]


Part No.	Shell Size	B DIA MAX	D DIA MIN	J		P ±10% b	L REF a	JO REF b	JW ±30% b
				MIN a	MAX b				
KTKK2470	8&8S	15.5 [.61]	6.3 [.25]	8 [.31]	5.0 [.20]	55 [2.17]	49 [1.93]	15 [.59]	1.0 [.04]
KTKK2471	10,10S&10SL	18.5 [.73]	9.3 [.37]	13 [.51]	6.0 [.24]	70 [2.76]	64 [2.52]	17 [.66]	1.0 [.04]
KTKK2472	12&12S	21.8 [.86]	12.7 [.50]	15 [.59]	7.2 [.28]	82 [3.23]	76 [2.99]	20 [.78]	1.0 [.04]
KTKK2473	14&14S	24.5 [.96]	14.2 [.56]	15 [.59]	7.2 [.28]	82 [3.23]	76 [2.99]	20 [.78]	1.0 [.04]
KTKK2474	16&16S	27.5 [1.08]	17.8 [.70]	19 [.75]	8.5 [.33]	95 [3.74]	86 [3.39]	25 [.98]	1.0 [.04]
KTKK2475	18	29.5 [1.16]	18.9 [.74]	19 [.75]	8.5 [.33]	95 [3.74]	86 [3.39]	25 [.98]	1.0 [.04]
KTKK2476	20	34.0 [1.34]	23.0 [.91]	24 [.94]	10.0 [.39]	120 [4.72]	108 [4.25]	30 [1.18]	1.2 [.05]
KTKK2477	22	37.3 [1.47]	23.7 [.93]	24 [.94]	10.0 [.39]	120 [4.72]	108 [4.25]	30 [1.18]	1.2 [.05]
KTKK2478	24	40.5 [1.59]	29.1 [1.15]	33 [.30]	15.8 [.62]	145 [5.71]	130 [5.12]	30 [1.18]	1.5 [.06]

DIMENSIONS:

mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
 1 PLC ± -
 2 PLC ± -
 3 PLC ± -
 4 PLC ± -
 ANGLES ± -



DWN

K. HOLAL

14OCT2016

CHK

N. NAGAR

14OCT2016

APVD

M. POPE

14OCT2016

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

CUSTOMER DRAWING

MATERIAL

SEE NOTES

FINISH

SEE NOTES



TE Connectivity

NAME

ADAPTOR ASSEMBLY

SIZE

A4

CAGE CODE

00779

DRAWING NO

C-KTKK2470-2478

RESTRICTED TO

—

SCALE

DNS

SHEET

1 OF 1

REV

3

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

COPYRIGHT 2016 By TE Connectivity