





REVISIONS				
P	LTR	DESCRIPTION	DATE	OWN APVD
A		PER ECO-18-020143	31DEC2018	MY GF
B		REVISED PER ECO-20-004723	03APR2020	REH GF



1 LABEL INFORMATION FOR 25 GIG PINS (-1 THRU -4): -1 SHOWN.


9 LABEL INFORMATION FOR 56 GIG PINS (-41 THRU -43): -41 SHOWN.




10 NO SLEEVING REQUIRED FOR 0.5M LENGTH (2340655-1 AND 4-2340655-1).

- SEE SHEET 2 FOR WIRING SCHEMATIC.
- PRODUCT AND PROCESSING MUST MEET THE REQUIREMENTS OF TE SPECIFICATION TEC-138-702.
- CABLE ASSEMBLY TO BE TESTED FOR OPENS, SHORTS AND PROPER EEPROM PROGRAMMING.

5 LABEL INFORMATION:



6 LABEL INFORMATION:



- TEST IN ACCORDANCE WITH IEEE802.3bj.
- DASH NUMBER 41 THRU 43 CONFORM TO 56G, PAM-4 IEEE802.3CD PERFORMANCE REQUIREMENTS.

8	32	500±25	1500 +50/-0	4-2340655-3
	32	500±25	1000 +50/-0	4-2340655-2
	32	250±25	500 +50/-0	4-2340655-1
7	32	1000±25	2000 +80/-0	2340655-4
	32	500±25	1500 +50/-0	2340655-3
	32	500±25	1000 +50/-0	2340655-2
	32	250±25	500 +50/-0	2340655-1
STANDARD	GAGE	"L2" mm	"L1" mm	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.


TE Connectivity

NAME: CABLE ASSEMBLY, QSFP TO (2) QSFP 25GIG, 32AWG

SIZE: A | 00779 | C=2340655

SCALE: 5:1 | SHEET 1 OF 2 | REV B

REVISIONS				
P	LTN	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-



### WIRING PATTERN

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: Y1 03SEP2018	
DIMENSIONS: mm		CHK: G. FRANKLIN 03SEP2018	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: G. FRANKLIN 03SEP2018	NAME: CABLE ASSEMBLY, QSFP TO (2) QSFP 25GIG, 32AWG
0 PLC ±		PRODUCT SPEC	SIZE: A
1 PLC ±		APPLICATION SPEC	CAGE CODE: 2340655
2 PLC ±		WEIGHT	RESTRICTED TO
3 PLC ±		CUSTOMER DRAWING	SCALE: 5:1
4 PLC ±			SHEET 2 OF 2
ANGLES ±			REV B
FINISH			