



D

С

4805 (3/13)





5	4	3	2	REVISIONS	1	
			-	P LTR DESCRIPTION A RELEASED PER ECO 20-004476 B REV PER ECO-21-008136	4-2-20 CT	FB FB
			-			
			BACKPLATE			
		MODULE HOUSING				
				0-80 UNF C SCREW (TOR	X DRIVE)	
			Star O.			
			SCALE	5:1		
	205 [5.21] [1.62]0.02]	05 🖛			<u></u>	
	. 064±.001 [1.63±0.02] 2 PLACES 2 1 2	05.21]	2			
	2-56 UNC-2B THREADED THRU HOLE 2 PLACES					
	2 PLACES				B	
					∇	
	2357976 SEE TABL	E	23	357976-2 see table scale 6:1		
	SCALE 6:					

MATERIAL: MODULE HOUSING AND BACKPLATE - ALUMINUM ALLOY SCREWS - 300 SERIES STAINLESS STEEL

- 2 FINISH: MODULE HOUSING AND BACKPLATE - CLEAR CHROMATE CONVERSION COATING SCREWS - PASSIVATED
- 3. SHIPPED IN KIT FORM. BACKPLATE SCREWS TO BE ASSEMBLED TO BACKPLATE.
- \triangle CIRCUIT IDENTIFICATION MARKING
- 5. DESIGNED TO BE USED WITH NanoRF CONTACTS 2302339-1


JURISDICTION	EAR	
CLASSIFICATION	EAR99	THIS DRAWING IS A
DATE OF MARKING	2 I OC T 2 O 2 I	DIMENSIONS:
ADMINISTRATION F	ONTAINS CONTROLLED TECHNICAL DATA SUBJECT TO THE EXPORT REGULATIONS (EAR). VIOLATIONS OF THESE EXPORT TIONS ARE SUBJECT TO CIVIL AND CRIMINAL PENALTIES.	INCHES[mm]

	. 432	.682	. 789	Ρ	Н	Η	Ρ	2357976-2	
	. 360	.490	. 540	Н	Р	Н	Ρ	2357976-1	
	A	В	С	1	2	3	4		
		OCATIO	N		E L E (P = P H = H	OST	ЭN	PART NUMBER	ļ
A CONTROLLED DOCUMENT. K. MILLER CHK K. DOWHOW	08JUL2019			. 7	E		TE C	onnectivity	
OPLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 1 APVD -	06		noRF MO POSITIO					RCARD, , VITA 67.3	
4 PLC ±- ANGLES ± 408-1630 FINISH WEIGHT -	16		age code dra 0779	wing no 	-	76		RESTRICTED TO -	
CUSTOMER DF	RAWING	i	I		SCALE	6:	1 SHE	et 1 of 2 Rev B	

D

С

B



А

4805 (3/13)

JURISDICTION EAR	
CLASSIFICATION EAR99	THIS DRAWING IS A CO
DATE OF MARKING 210CT2021	DIMENSIONS:
THIS DOCUMENT CONTAINS CONTROLLED TECHNICAL DATA SUBJECT TO THE EXPORT ADMINISTRATION REGULATIONS (EAR). VIOLATIONS OF THESE EXPORT LAWS AND REGULATIONS ARE SUBJECT TO CIVIL AND CRIMINAL PENALTIES.	
	MATENIAL

C	CONTROLLE	D DOCUMENT.	DWN 08JUL2019 К. MILLER Снк 16AUG2019 К. DOWHOWER	_		E T	E TE	Connec	c t i v i t	у
1	0 PLC 1 PLC 2 PLC	ANCES UNLESS SE SPECIFIED: ±- ±- ±-	APVD - - PRODUCT SPEC 108-163006				, DAUGH 047 CAB			67.3
	3 PLC 4 PLC ANGLES FINISH	±.005[0.13] ±- ±	APPLICATION SPEC 408-163016 WEIGHT _	size A 1	cage code	DRAWING NO				RESTRICTED T
			CUSTOMER DRAWING		1		scale 6:1	SHEET ,	> ^{OF} 2	REV B

P2A	2.107[53.52]
P2B	2.663[67.64]
P3A	3.795[96.39]
P3B	4.351[110.51]
P 4 A	4.929[125.19]
P4B	5.485[139.31]
P5A	6.062[153.99]
P5B	6.618[168.11]
P6A	7.196[182.79]
P6B	7.752[196.91]
POSITION	D I M " X "

P 2 A	2.107[53.52]
P2B	2.663[67.64]
РЗА	3.795[96.39]
P3B	4.351[110.51]
P 4 A	4.929[125.19]
P 4 B	5.485[139.31]
P5A	6.062[153.99]
P5B	6.618[168.11]
P 6 A	7.196[182.79]
P 6 B	7.752[196.91]
POSITION	DIM "X"

			1			
		REVISIONS				
Ρ	LTR	DESCRIPTION		DATE	DWN	APVD
	-	SEE SHEET 1		-	-	-

B

В