Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	Wu, Cc	**Contact Title**	Engineer Product Compliance china
Company Unique ID	TE Connectivity	**Response Date**	2017-12-20	**Contact Email**	cc.wu@te.com		
Contact Phone Number		86-2124071672					

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	1877285-6	**Amount**	2462.5168	**Version**	-	**Identity**	
Manufacturer Item Name	06P EP SHRD HDR ASMY, WHITE	**Weight Uom**	mg	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed						
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed						

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	Brass #4 wire, 100-86, Tin Plated				6.0	159.4778	mg	
Material	2	Tin Plate				6.0	0.4779	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	6.0	0.47661	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	6.0	9.558E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	6.0	3.3453E-4	mg	
Material	2	Nickel Plate				6.0	0.6999	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	6.0	0.0013998	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	6.0	6.999E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	6.0	0.6978	mg	
Material	2	Brass				6.0	158.3	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	6.0	0.001583	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	6.0	44.35962	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	6.0	0.07915	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	6.0	0.01583	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	6.0	0.07915	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	6.0	0.1583	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	6.0	113.1845	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	6.0	0.001583	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	6.0	0.01583	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	6.0	7.915E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	6.0	0.3166	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	6.0	0.007915	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	6.0	0.07915	mg	

Sub-Item	1	EP Header Housing,Shrouded,6 Position				1.0	1505.65	mg	
Material	2	PBT-I-GF30-FR(17)				1.0	1505.65	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	1.0	15.0565	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	40.1555	1.0	604.60129	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.1	1.0	1.50565	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	7.52825	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.0	1.0	60.226	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	15.0565	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	4.0	1.0	60.226	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	1.0	1.0	15.0565	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.02	1.0	0.30113	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.18	1.0	2.71017	mg	
Substance	3	Zinc sulfide (ZnS)	Supplier	1314-98-3	4.0	1.0	60.226	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.0030	1.0	0.0451695	mg	
Substance	3	C.I. Pigment Blue 28	Supplier	1345-16-0	0.01	1.0	0.15056	mg	
Substance	3	C.I. Pigment Brown 24	Supplier	68186-90-3	0.01	1.0	0.15056	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	12.0	1.0	180.678	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	32.0	1.0	481.808	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.015	1.0	0.22585	mg	
Substance	3	Lead oxide (lead monoxide)	Lead/Lead Compounds	1317-36-8	0.0020	1.0	0.030113	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0030	1.0	0.0451695	mg	
Substance	3	Arsenic oxide (As2O3)	Arsenic oxide (As2O3)	1327-53-3	0.0015	1.0	0.02258475	mg	