


REVISIONS					
P	LTR	DESCRIPTION	DATE	OWN	APP'D
A		INITIAL REL PER LC20-0051-20	06MAY2020	DM	BJ
A1		LC20-0059-20 / ECO-20-006903	15MAY2020	DM	BJ




- WIRE HARNESS SHALL BE BUILT TO UL STANDARD AND SHALL BE LISTED TO UL STANDARD 9703.
- HARNESS SHALL CONFIRM TO UL 4703 PV RATING. THIS HARNESS RATED FOR OPERATION AT 2 kV DC. UV RESISTANT AND DIRECT BURIAL RATED AS REQUIRED.
- CONNECTORS PREFABRICATED MARKINGS ARE NOT INDICATIVE OF THE (POSITIVE OR NEGATIVE) TYPE OF HARNESS ASSY.

4 PRODUCT LABEL MARKING:  
LABEL TEXT INK STAMPED ON LABEL TO  
READ AS BELOW. SEE TABLE FOR VALUES.

[TE LOGO]  
[TE PART NO]  
[SERIAL NO]  
[DATE CODE]

 2364039-1 [SERIAL NO] [DATE CODE]	PVH-HP001-025BK1SA51	2364039-1
LABEL MARKING 4	DESCRIPTION	PART NO

1	SERIAL NO LABEL, UL LISTED, ADHESIVE	7
A/R	#8 awg WIRE, RHW-2 COPPER STRANDED, 2 kV RATED, WHITE	6
1	TEE JOINT, OVERMOLDED, XLPE/PVC	5
1	30A OVERMOLDED FUSE ASSEMBLY	4
2	15A OVERMOLDED FUSE ASSEMBLY	3
3	MALE PLUG, MC4	2
1	FEMALE PLUG, MC4	1
-1	DESCRIPTION	ITEM NO
QTY	PARTS LIST	

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN D. MURUGIAH 06MAY2020	 TE Connectivity	
DIMENSIONS: INCHES		CHK S. RAHMAN 06MAY2020	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APP'D B. JOHNSON 06MAY2020	PRODUCT SPEC	
MATERIAL SEE BOM		FINISH -	APPLICATION SPEC	
		WEIGHT 0	RESTRICTED TO	
		CUSTOMER DRAWING	SCALE NTS	
		SIZE A2	CAGE CODE 00779	DRAWING NO C-2364039-1
		SHEET 1 of 1	REV A1	