



Table of Dimensions										
Part Description	H			HW(Y)		R	W		P	
	a	a ¹	b	a	b	b	a	b	a	b
	Min	Min	Max		±15%	±10%		±20%		±10%
205A014-4	1.11 (28)	0.93 (23.6)	0.49 (12.7)	-	0.07 (1.8)	0.18 (4.5)	-	0.15 (3.8)	-	9 (229)
*205A045-4	1.66 (42)	1.61 (40.9)	0.75 (19.5)	-	0.07 (1.8)	1.42 (36)	-	0.1 (2.5)	-	20 (508)
205A046-4	1.66 (42)	1.61 (40.9)	0.75 (19.5)	-	0.08 (2.0)	1.42 (36)	-	0.17 (4.3)	-	20 (508)
205A047-4	2.8 (71)	2.74 (69.6)	1.16 (30.0)	-	0.10 (2.54)	1.42 (36)	-	0.18 (4.6)	-	22 (560)
205A058-4	3.56 (90)	3.5 (88.9)	1.48 (38.0)	-	0.08 (2.0)	1.42 (36)	-	0.2 (5.1)	-	22 (560)

NOTES:

- Dimensions in inches (millimeters)
- Dimensions in table below as follows:
a = as supplied
a¹ = as supplied, coated
b = after free recovery
- Material -4 meets requirements of PPS 3011/4.
Adhesive /97 meets requirements of PPS 3012/48.
- Printing: "P-137-4-MSHA" in raised letters molded on outer surface with Raychem-Product Description.
- Packaging: Packed in poly bag.
- Labeling: Quantity, Description, and Batch Number.

*This product is only available in /42 adhesive coating.