

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	30AUG2017	YC	CW

M4 SCREW, RECOMMENDED  
TIGHTENING TORQUE 1.2N.m  
M4 螺丝, 推荐拧紧力矩1.2N.m

NOTES:

1. TECHNICAL CHARACTERISTICS:  
INSULATION MATERIAL: PC  
RATED VOLTAGE: 500V  
RATED CURRENT: 16A  
INSULATION RESISTANCE:  $\geq 400M\Omega$   
RATED IMPULSE VOLTAGE: 6KV  
POLLUTION DEGREE: 3  
FLAMMABILITY: UL94V-0  
MATING CYCLES: 500 CYCLES  
WIRE RANGE:  $0.14mm^2 \sim 4mm^2$  (AWG26-AWG12)  
CONTACT TYPE: CRIMP CONTACT

2. CONTACTS NEED TO BE ORDERED SEPARATELY.  
(ORDER No. REFER TO DRAWING: T20300X20XX000)

4X M3 SCREW, RECOMMENDED  
TIGHTENING TORQUE 0.5N.m  
4X M3 螺丝, 推荐拧紧力矩0.5N.m

注释:

1. 技术参数:  
绝缘材料: PC  
额定电压: 500V  
额定电流: 16A  
绝缘电阻:  $\geq 400M\Omega$   
脉冲电压: 6KV  
污染等级: 3  
阻燃等级: UL94V-0  
插拔次数: 500次  
接线范围:  $0.14mm^2 \sim 4mm^2$  (AWG26-AWG12)  
接线类型: 冷压接

2. 端子需要单独订购.  
(订货号参考图面: T20300X20XX000)

PANEL CUT FOR INSERTS FOR USE  
WITHOUT HOODS/ HOUSINGS  
不使用防护外壳时芯件安装平面开孔图

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±-
	1 PLC ±-
	2 PLC ±-
	3 PLC ±-
	4 PLC ±-
	ANGLES ±-
MATERIAL	FINISH
-	-
-	-

T2051283201-007	HEEE-064-F 65-128	HEEE-064 FEMALE INSERT 65-128 HEEE-064 母插 65-128
PART NUMBER 料号	PART DESCRIPTION 描述	
<p>THIS DRAWING IS A CONTROLLED DOCUMENT.</p> <p>DWN 30AUG2017 YORK CHEN</p> <p>CHK 30AUG2017 GINO YAO</p> <p>APVD 30AUG2017 CHRIS WANG</p> <p>PRODUCT SPEC 108-137068</p> <p>APPLICATION SPEC 114-137068</p> <p>WEIGHT -</p> <p>CUSTOMER DRAWING</p>		
<p>NAME HEEE-064-F 65-128</p> <p>SIZE A3</p> <p>CAGE CODE 00779</p> <p>DRAWING NO T2051283201007</p> <p>RESTRICTED TO -</p>		
<p>SCALE 1:1</p> <p>SHEET 1</p> <p>OF 1</p> <p>REV A</p>		

1470-19 (3/13)