

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	25MAR2015	DW	CW
	B	ECR-15-018270	08DEC2015	DW	CW
	C	ECR-21-111798	29SEP2021	WQR	CW

NOTES:

1. TECHNICAL CHARACTERISTICS:
 INSULATION MATERIAL: PC
 RATED VOLTAGE: 160V
 RATED CURRENT: 10A
 INSULATION RESISTANCE: $\geq 400M\Omega$
 RATED IMPULSE VOLTAGE: 2.5KV
 POLLUTION DEGREE: 2
 FLAMMABILITY: UL94V-0
 MATING CYCLES: 500 CYCLES
 OPERATION TEMPERATURE: $-40\sim+125^{\circ}C$
 WIRE RANGE: $0.14\sim 2.5\text{ mm}^2$ (26~14 AWG)
 CONTACT TYPE: CRIMP CONTACT



2. CONTACT NEED TO BE ORDERED SEPARATELY.
 (ORDER No. REFER TO DRAWING: T20200X10XX000)

注释:

1. 技术参数:
 绝缘材料: PC
 额定电压: 160V
 额定电流: 10A
 绝缘电阻: $\geq 400M\Omega$
 额定脉冲电压: 2.5KV
 污染等级: 2
 阻燃等级: UL94V-0
 插拔次数: 500次
 工作温度: $-40\sim+125^{\circ}C$
 接线范围: $0.14\sim 2.5\text{ mm}^2$ (26~14 AWG)
 接线类型: 冷压接

2. 端子需要单独订购.
 (订货号参考图面: T20200X10XX000)

HMN-017-M	T2111172101-000
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	25MAR2015	 TE Connectivity	
DIMENSIONS:		CHK	25MAR2015		
mm		APVD	25MAR2015		
		PRODUCT SPEC	108-137062		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	HMN-017-M		RESTRICTED TO
0 PLC \pm		APPLICATION SPEC	114-137062		
1 PLC \pm		WEIGHT	-		-
2 PLC \pm		SIZE	A3	CAGE CODE	
3 PLC \pm		114-137062		DRAWING NO	T2111172101000
4 PLC \pm		Customer Drawing		SCALE	3:2
ANGLES \pm		-		SHEET	1 OF 1
FINISH		-		REV	C

1470-19 (3/13)