







REVISIONS				
#	DATE	DESCRIPTION	DATE	APP'D
A1		RELEASE PER ECN-21-105275	02JUN2021	DFS SH






NUMBER OF POLES	1 POSITION	4 POSITION
INTERFACE TE PART NUMBER (BASIC)	208-160011	208-160010
PICTURE		
TE PART NUMBER (BASIC)	PN: 2355843	PN: 2338212
PRODUCT DESCRIPTION	PLUG ASSY SEALED COAX	PLUG ASSY SEALED COAX
CONTACT DRAWING	PN: 2298488 MATE-AX 180DEG SOCKET CONTACT CABLE RTK031 WIRE SIZE: MAX Ø2.1mm PN: 2298510 MATE-AX 180DEG SOCKET CONTACT CABLE RG174 WIRE SIZE: MAX Ø1.6mm	PN: 2298488 MATE-AX 180DEG SOCKET CONTACT CABLE RTK031 WIRE SIZE: MAX Ø2.1mm PN: 2298510 MATE-AX 180DEG SOCKET CONTACT CABLE RG174 WIRE SIZE: MAX Ø1.6mm
PICTURE		
TE PART NUMBER (BASIC)	PN: 2374559	PN: 2338211
PRODUCT DESCRIPTION	CAP ASSY SEALED COAX	CAP ASSY SEALED COAX
CONTACT DRAWING	PN: 2298490 MATE-AX 180DEG PIN CONTACT CABLE RTK031 WIRE SIZE: MAX Ø2.1mm PN: 2298511 MATE-AX 180DEG PIN CONTACT CABLE RG174 WIRE SIZE: MAX Ø1.6mm	PN: 2298490 MATE-AX 180DEG PIN CONTACT CABLE RTK031 WIRE SIZE: MAX Ø2.1mm PN: 2298511 MATE-AX 180DEG PIN CONTACT CABLE RG174 WIRE SIZE: MAX Ø1.6mm
PICTURE		
TE PART NUMBER (BASIC)	-	PN: 2339729
PRODUCT DESCRIPTION	-	BULKHEAD INLINE RUGGED COAX
CONTACT DRAWING	-	PN: 2298490 MATE-AX 180DEG PIN CONTACT CABLE RTK031 WIRE SIZE: MAX Ø2.1mm PN: 2298511 MATE-AX 180DEG PIN CONTACT CABLE RG174 WIRE SIZE: MAX Ø1.6mm
PICTURE		
TE PART NUMBER (BASIC)	PN: 2355844	PN: 2356408
PRODUCT DESCRIPTION	VERTICAL COAX HEADER	VERTICAL COAX HEADER
CONTACT DRAWING	PN: 2356413 AS16 COAX PIN	PN: 2356413 AS16 COAX PIN

THIS DRAWING IS NOT SUBJECT TO CONSTANT CHANGING SERVICE AND DOES NOT LAY CLAIM TO BE COMPLETE. FOR DEFINITE SPECIFICATION SEE RESPECTIVE TE CUSTOMER DRAWINGS. FURTHER VERSIONS ON INQUIRY.


THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: DEEPAK A R 16OCT2020	
DIMENSIONS: mm		CHK: DANIEL STACK 20OCT2020	
TOLERANCES UNLESS OTHERWISE SPECIFIED		APVD: S. HELM 2JUNE2021	NAME: AS16 COAX PRODUCT FAMILY GROUP DRAWING
0 PLC ±0.1		PRODUCT SPEC	SIZE: A1
1 PLC ±0.05		108-94799	CAGE CODE: 00779
2 PLC ±0.01		APPLICATION SPEC	DRAWING NO: 2381263
3 PLC ±0.001		114-94667	RESTRICTED TO: CUSTOMER
4 PCC ±0.0001		WEIGHT: -	SCALE: 1:2
ANGLES		RESTRICTED CUSTOMER	SHEET 1 OF 2
FINISH			REV: A1

REPLACEMENT PARTS		
NUMBER OF POLES	1 POSITION	4 POSITION
CAP TPA	 SCALE 1:1	 SCALE 1:1
TE PART NUMBER	PN: 2374575-1	PN: 2338216-1
COUNTERPART	SUITABLE FOR 1P COAX CAP HOUSING	SUITABLE FOR 4P COAX CAP HOUSING AND BLUKHEAD INLINE RUGGED COAX
PLUG TPA	 SCALE 1:1	 SCALE 1:1
TE PART NUMBER	PN: 2355835-1	PN: 2338218-1
COUNTERPART	SUITABLE FOR 1P COAX PLUG HOUSING	SUITABLE FOR 4P COAX PLUG HOUSING

ACCESSORIES:		
NUMBER OF POLES	1 POSITION	4 POSITION
CAP BACKSHELL	-	
TE PART NUMBER	-	PN: 2292862-1
COUNTERPART	-	SUITABLE FOR 4P COAX CAP HOUSING AND BLUKHEAD INLINE RUGGED COAX
CABLE EXIT DIRECTION	-	180°
CORRUGATED TUBE	-	SMOOTH
PLUG BACKSHELL	-	
TE PART NUMBER	-	PN: 2292799-1
COUNTERPART	-	SUITABLE FOR 4P COAX PLUG HOUSING
CABLE EXIT DIRECTION	-	180°
CORRUGATED TUBE	-	SMOOTH

MOUNTING CLIP	 SCALE 1:1	 SCALE 1:1	 SCALE 1:1	BLIND PLUG	 SCALE 2:1	EXTRACTION TOOL	 SCALE 1:4
TE PART NUMBER	PN: 1924487-1	PN: 1924487-2	PN: 1924487-3	TE PART NUMBER	PN: 776363-1	TE PART NUMBER	PN: 776441-1
PRODUCT DESCRIPTION	AS16 MOUNTING CLIP, STRAIGHT, 20.5mm, FIR TREE STUD MOUNT	AS16 MOUNTING CLIP, STRAIGHT, 20.5mm, FIR TREE STUD MOUNT ANTI-ROTATION	AS16 MOUNTING CLIP, STRAIGHT, 11mm, FIR TREE STUD MOUNT	USED ON	4P COAX CAP AND PLUG HOUSING, BLUKHEAD AND INLINE RUGGED COAX	PRODUCT DESCRIPTION	TOOL USED FOR REMOVAL OF TPA, TERMINAL AND BACKSHELL

REVISIONS				
#	LY#	DESCRIPTION	DATE	OWN / APVD
-	-	SEE SHEET 1	-	-

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: DEEPAK A R 16OCT2020	
DIMENSIONS: mm		CHK: DANIEL STACK 20OCT2020	
TOLERANCES UNLESS OTHERWISE SPECIFIED		APVD: S. HELM 2JUNE2021	NAME: AS16 COAX PRODUCT FAMILY GROUP DRAWING
0 PLC ±0.1		PRODUCT SPEC	SIZE: A1
1 PLC ±0.1		108-94799	CAGE CODE: 00779
2 PLC ±0.05		APPLICATION SPEC	DRAWING NO: 2381263
3 PLC ±0.001		114-94667	RESTRICTED TO: RESTRICTED CUSTOMER
4 PLC ±0.0001		WEIGHT: -	SCALE: 1:2
ANGLES FINISH		RESTRICTED CUSTOMER	SHEET 2 OF 2

THIS DRAWING IS NOT SUBJECT TO CONSTANT CHANGING SERVICE AND DOES NOT LAY CLAIM TO BE COMPLETE. FOR DEFINITE SPECIFICATION SEE RESPECTIVE TE CUSTOMER DRAWINGS. FURTHER VERSIONS ON INQUIRY.