

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20


BY -

ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	22DEC2017	YC	CW


ASSEMBLY STATE OF THE PRODUCT, FOR REFERENCE
产品装配状态, 供参考







M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5 N.m
M3螺丝, 推荐锁紧力矩 0.5 N.m



FOR $\varnothing 3-6$ mm CABLE
用于直径 $\varnothing 3-6$ mm 电缆线



FOR $\varnothing 6-9.5$ mm CABLE
用于直径 $\varnothing 6-9.5$ mm 电缆线



SCALE 3:2

NOTES:

- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 50V
RATED CURRENT: 10A
RATED IMPULSE VOLTAGE: 0.8KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
CONTACT TYPE: CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20200X10XX000)

注释:

- 技术参数:
绝缘材料: PC
额定电压: 50V
额定电流: 10A
额定脉冲电压: 0.8kV
污染等级: 3
阻燃等级: UL94V-0
接线范围: 0.14-2.5 mm² (26-14 AWG)
接线类型: 冷压接
- 端子需要单独订购.
(订货号参考图面: T20200X10XX000)

T2580011154-701

PIN-Q2-M1

QUINTAX MALE CONTACT 1-POS, 10A
QUINTAX 1-POS 公针, 10A

PART NUMBER
料号

PART DESCRIPTION
描述

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 22DEC2017

YORK CHEN

CHK 22DEC2017

GINO YAO

APVD 22DEC2017

CHRIS WANG

PRODUCT SPEC

108-137067

APPLICATION SPEC

114-137067

WEIGHT

-

CUSTOMER DRAWING

TE

TE Connectivity

NAME
QUINTAX CONTACT 1-POS, 10A
PIN-Q2-M1

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 - © T2580011154701 -

SCALE 2:1 SHEET 1 OF 1 REV A