



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	05FEB2021	J.G	I.Y
	A1	REVISE	12OCT2021	K.W	W.Z




SCALE 5:1
16-18 AWG SIZE SHOWN


- 1 MATERIAL: COPPER ALLOY 0.300 THICKNESS.
- 2 FINISH: SELECTIVE TIN 0.5 μ m MINIMUM OVER NICKEL 1.00 μ m MINIMUM OVERALL.
- 3 FINISH: SELECTIVE HARD GOLD 0.60 μ m MINIMUM WITH SELECTIVE TIN 0.5 μ m MINIMUM OVER NICKEL 1.00 μ m MINIMUM OVERALL.
4. STRIP PARTS ARE REELED 3000 PARTS PER REEL.
5. TERMINAL FOR USE ON XRC & ML-XT CONNECTOR ASSEMBLIES.



SECTION A-A
SCALE: 10:1
INSULATION CRIMP



SECTION B-B
SCALE: 10:1
CONDUCTOR CRIMP



0.22mm-0.50mm	20-24 AWG	20-24	2.02	2.25	2.60	2.43	SELECTIVE GOLD		COPPER ALLOY 	845250067	5-2600021-5
0.22mm-0.50mm	20-24 AWG	20-24	2.02	2.25	2.60	2.43	NICKEL			845250063	5-2600021-3
1.40mm-2.54mm	0.5-1.0 mm ²	0.5-1.0	2.90	3.71	2.92	3.40	SELECTIVE GOLD			845250057	4-2600021-5
1.40mm-2.54mm	0.5-1.0 mm ²	0.5-1.0	2.90	3.71	2.92	3.40	NICKEL			845250053	4-2600021-3
2.41mm-3.81mm	14-18 AWG	14-18	3.43	4.05	4.60	5.68	SELECTIVE GOLD			845250046	3-2600021-5
2.41mm-3.81mm	14-18 AWG	14-18	3.43	4.05	4.60	5.68	NICKEL			845250025	3-2600021-3
1.90mm-3.30mm	14-18 AWG	14-18 TW	3.27	3.95	3.38	4.57	SELECTIVE GOLD			845250039	2-2600021-5
1.90mm-3.30mm	14-18 AWG	14-18 TW	3.27	3.95	3.38	4.57	NICKEL			845250017	2-2600021-3
1.40mm-2.16mm	16-18 AWG	16-18	2.85	3.64	2.82	3.48	SELECTIVE GOLD			845250032	1-2600021-5
1.40mm-2.16mm	16-18 AWG	16-18	2.85	3.64	2.82	3.48	NICKEL			845250009	1-2600021-3
INSULATION RANGE	WIRE RANGE	STAMP NO.	D	C	B	A	FINISH		MATERIAL	ALIAS P/N	PART NUMBER
			WIRE CRIMO		INSULATION CRIMP						

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 120CT2021 CHK K.W W.ZHANG APVD 120CT2021 W.ZHANG		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.20		NAME XRC SOCKET W/SNAP WINDOW			
		PRODUCT SPEC -		SIZE A2			
MATERIAL - -		APPLICATION SPEC -		CAGE CODE 00779		DRAWING NO C=2600021	
FINISH - -		WEIGHT -		RESTRICTED TO -		SCALE 5:1	
CUSTOMER DRAWING				SHEET		REV	
				1 of 1		A1	