

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	27APR2017	DW	CW





NOTES/注解：

1. TECHNICAL CHARACTERISTICS/技术参数：
   SHELL MATERIAL/主体材料 : NICKEL PLATED BRASS/铜镀镍
   SEAL MATERIAL/密封材料: RUBBER, BLACK
   PINCH RING MATERIAL/夹紧件材料:NYLON,GREY
   OPERATION TEMPERATURE/工作温度: -40°C-+100°C
   PROTECTION DEGREE/防护等级: IP68
   WIRE RANGE/夹线范围: 18-25 mm



T3707320103-000	DLX-32-MC (18~25) 电磁屏蔽金属接头 M32 (18-25)
PART NUMBER 料 号	PART DESCRIPTION 描 述

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL: -
FINISH: -

DWN DAVID WANG 27APR2017
CHK CHRIS WANG 27APR2017
APVD XIANG XU 27APR2017
PRODUCT SPEC: -
APPLICATION SPEC: -
WEIGHT: -

CUSTOMER DRAWING

TE Connectivity

NAME DLX-32-MC (18~25)

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-T3707320103000	-

SCALE 1:1 SHEET 1 OF 1 REV A