



MODEL 406

TUBULAR PROBE

- FDA pre-amendment status
- 400 series nominal resistance response curve
- 2252.4 Ohm resistance @ 25°C (including lead wire resistance)
- Interchangeable $\pm 0.1^{\circ}\text{C}$, 25°C to 45°C
- Tested to $\pm 0.1^{\circ}\text{C}$, 0°C to 70°C for laboratory use
- Pressed disk ceramic sensor
- High sensitivity to temperature change
- 316 Stainless Steel tube
- 1/4" phone plug connector
- 3.2mm (0.125") tube diameter

FEATURES

- Standard 400 series resistance response
- Standard 1/4" phone plug connector
- Reuse after cleaning

400-series tubular temperature probe

APPLICATIONS

- Continuous patient monitoring
- Rectal temperature measurement


MODEL 406

Tubular Probe

PERFORMANCE SPECS

Parameter	Units	Value
Resistance @ 25°C (including lead resistance)	Ohms	2252.4
Tolerance 0°C to 70°C	°C	± 0.1
Recommended equilibration time before measurement	Minutes	> 3
Insulation Resistance (500 VAC for 1 Sec.)	Mega Ohms	> 100

MECHANICAL DETAILS



RESISTANCE V TEMPERATURE

Temp °C	K-Ohms	Temp °C	K-Ohms	Temp °C	K-Ohms	Temp °C	K-Ohms
0	7.3554	18	3.0814	36	1.4124	54	0.6983
1	6.9894	19	2.9444	37	1.3554	55	0.6729
2	6.6444	20	2.8144	38	1.3014	56	0.6485
3	6.3194	21	2.6904	39	1.2494	57	0.6252
4	6.0114	22	2.5724	40	1.2004	58	0.6028
5	5.7194	23	2.4604	41	1.1524	59	0.5813
6	5.4444	24	2.3544	42	1.1074	60	0.5607
7	5.1834	25	2.2524	43	1.0644	61	0.5409
8	4.9374	26	2.1564	44	1.0234	62	0.5219
9	4.7034	27	2.0644	45	0.9842	63	0.5037
10	4.4824	28	1.9774	46	0.9466	64	0.4862
11	4.2734	29	1.8944	47	0.9106	65	0.4694
12	4.0744	30	1.8154	48	0.8762	66	0.4533
13	3.8864	31	1.7394	49	0.8432	67	0.4378
14	3.7084	32	1.6674	50	0.8117	68	0.4229
15	3.5394	33	1.5994	51	0.7815	69	0.4086
16	3.3784	34	1.5334	52	0.7526	70	0.3949
17	3.2264	35	1.4714	53	0.7249		

MODEL 406

Tubular Probe

ORDERING INFORMATION

Part Number	Description	Ω @25°C
081106	406 PROBE,THERM	2252.4

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
1711 139th Lane NW
Andover, MN 55304
Tel: +1 763 689 4870
Fax: +1 763 689 5033
Email: customercare.ando@te.com

te.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties (MEAS), American Sensor Technologies (AST), TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.