



MEAS THERMOCOUPLE PROBE

- ◆ Variety of Configurations
- ◆ Single and Dual Junctions
- ◆ Stainless Steel Case
- ◆ Custom Designs Available with:
 - » Degree Specific Case Bends
 - » Miniature Size
 - » Cut-to-length Cases
 - » Connector Options

Features

- ◆ Sheath Styles:
 - » Stainless Steel
- ◆ Joint Types, Single and Dual:
 - » J, K, T, E
 - » Grounded or Ungrounded
- ◆ Sheath Diameters:
 - » 0.125", 0.188", 0.250"
- ◆ Leadwire/Cable Options

Applications

- ◆ Process
- ◆ Aerospace
- ◆ Defense
- ◆ Hot Melt

The Thermocouple Probe is constructed with a Stainless Steel case. The sensing junction is embedded into the tip of the sheath. With the junction located in the tip of the case this is the area that needs to be in contact with the process to obtain correct temperature measurement. Fittings associated with the probe designs are related to the mounting technique required by your application. These sensors can be utilized in many different industries and applications. Probe sensors are ideal for immersion in processes.

Dimensions



'D' = Sheath Diameter
 'L' = Sheath Length
 'Y' = Leadwire/Cable Length

Performance Specifications

Insulation Resistance – Ungrounded Models:
 1,000 megohms @ 500 V, leads to case

Vibration:
 Withstands 5 to 500 Hz at 3 g-level peak for 3 hours. Per ASTM E 644, Sec. 10.

Shock:
 Withstands 50 g-level peak sine wave shock of 11 milliseconds duration. Per ASTM E 644, Sec. 11

Pressure Rating:
 1,500 psi

Thermocouple Temperature Accuracy Specifications:

Type	Temp Range	Standard Limits of Error	Special Limits of Error
T	-200 to 0°C	±1°C or 1.5%	Not ASTM Defined
	0 to 350°C	±1°C or 0.75%	±0.5°C or 0.4%
J	0 to 750°C	±2.2°C or 0.75%	±1.1°C or 0.4%
E	-200 to 0°C	±1.7°C or 1%	Not ASTM Defined
	0 to 900°C	±1.7°C or 0.5%	±1°C or 0.4%
K	-200 to 0°C	±2.2°C or 2%	Not ASTM Defined
	0 to 1,250°C	±2.2°C or 0.75%	±1.1°C or 0.4%

Ordering Information

Thermocouple Probe			
Model	Temperature Range		
200M	Moderate: -50 to 250°C (-58 to 482°F)		
200H	High: Mineral Insulated		
Model	Thermocouple Type	Junction	Color Code
J	J	Single	Red/White [Constantan/Iron]
K	K	Single	Red/Yellow [Alumel/Chromel]
T	T	Single	Red/Blue [Constantan/Copper]
E	E	Single	Red/Purple [Constantan/Chromel]
JJ	JJ	Dual	Red/White // Red/White
KK	KK	Dual	Red/Yellow // Red/Yellow
TT	TT	Dual	Red/Blue // Red/Blue
EE	EE	Dual	Red/Purple // Red/Purple
Model	Junction Style		
G	Grounded Junction		
U	Ungrounded Junction		
Model	Limits of Error		
A	Standard Limits of Error		
B	Special Limits of Error		
Model	'D' Sheath Diameter		
A	.125" Diameter (Single Junction Only)		
B	.188" Diameter		
C	.250" Diameter		
Model	Sheath Material		
B	Stainless Steel		
E	Inconel (H Only)		
Model	'L' Sheath Length		
----	Define 'L' Length in Inches Note: Minimum 1.5" / Maximum 96.0" Example: (12.0 = 12.0"; 28.5 = 28.5")		
Model	'Y' Leadwire/Cable Options		
N	No Options, Solid TFE Leadwires (36.0" Standard)		
W	Leadwire Options		

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
Tel: 800-522-6752
customercare.ando@te.com

EUROPE

Measurement Specialties (Europe), Ltd.,
a TE Connectivity Company
Tel: 800-440-5100
customercare.ftny@te.com

ASIA

Measurement Specialties (China), Ltd.,
a TE Connectivity Company
Tel: 0400-820-6015
customercare.chdu@te.com

te.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, MEAS, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.