


**TWO CONDUCTOR CABLE, HALOGEN FREE INSULATION, SHIELDED AND HALOGEN FREE JACKETED,
600 VOLT AC, 105°C**

The complete requirements for procuring the wire described herein shall consist of this document.



Part Description	Nominal Conductor Cross Sectional Area (mm ²)	Component Wire Description	Maximum Resistance @ 20°C (Ohms/km)	Shield Size (mm)	Jacket Thickness (mm)		Overall Diameter (mm)			Maximum Weight (kg/km)
					Min	Nom	Min	Nom	Max	
VG 95218 T023 C034	0.15	VG 95218 T020 E129	135.0	0.10	0.15	0.28	2.92	3.06	3.22	15.9
VG 95218 T023 C001	0.25	VG 95218 T020 E019	85.6	0.10	0.15	0.28	3.13	3.29	3.45	18.9
VG 95218 T023 C002	0.40	VG 95218 T020 E029	51.5	0.13	0.15	0.28	3.60	3.78	3.98	26.5
VG 95218 T023 C003	0.50	VG 95218 T020 E039	40.9	0.13	0.15	0.28	3.76	3.92	4.16	30.4
VG 95218 T023 C004	0.60	VG 95218 T020 E049	31.7	0.13	0.15	0.28	3.95	4.16	4.37	33.3
VG 95218 T023 C005	0.75	VG 95218 T020 E059	27.2	0.13	0.15	0.28	4.19	4.32	4.63	37.4
VG 95218 T023 C006	1.00	VG 95218 T020 E069	20.4	0.13	0.15	0.28	4.38	4.61	4.84	42.3
VG 95218 T023 C007	1.20	VG 95218 T020 E079	15.6	0.13	0.15	0.28	4.73	4.98	5.23	50.2
VG 95218 T023 C008	1.50	VG 95218 T020 E089	14.0	0.13	0.15	0.28	5.02	5.28	5.54	56.7
VG 95218 T023 C009	2.00	VG 95218 T020 E099	10.7	0.13	0.15	0.28	5.55	5.84	6.13	68.7
VG 95218 T023 C010	2.50	VG 95218 T020 E109	8.37	0.13	0.15	0.28	5.92	6.22	6.54	81.5
VG 95218 T023 C011	3.00	VG 95218 T020 E119	6.71	0.13	0.15	0.28	6.35	6.68	7.01	95.0

*Zerohal' is a registered trademark of Tyco Electronics Corporation.

COLOUR CODE: Components for the above cables shall be VG 95218 T020 EXX9
Where XX = Size code, 9 = Component colour white
i.e. Components for VG 95218 T023 C001 shall be VG 95218 T020 E019
Jacket colour shall be black

PERFORMANCE REQUIREMENTS : Shall be tested to the issue in effect of WSD 955.
Shall meet the requirements of the issue in effect of VG 95218 Part 23 Specification for Type C cables.

APPROVAL: Electronic sign off - no signatures will appear.