



Für diese Zeichnung behalten wir uns das Urheberrecht gemäß DIN ISO 16016 vor

Technical Data:

Case Material	PA GF black
Switch Lever Material	PA GF red
Min.Insulation Resistance	100MΩ
Dielectric Withstanding Voltage	1050V-1min.
Max.Contact Drop during Resistive Load	150mV
Voltage	up to 32VDC
Duty Rating	2x 200A
Overload	2x 500A-180sec.
	2x 1000A-30sec.
Sealing	IP 67/ IEC 529
Vibration	4G/ 50-2000Hz
Shock G-Lever	6G/ 11ms
Weight	~330g / 0.72 pound
Temperature Range	-40°C to +85°C
Wire Section (At Nominal Load)	min. 70mm ²
Mounting Position	optional
Switch Lever	removeable
Torque (Main Terminals)	12-13Nm

	Datum	Name	Allgemeintoleranz	Maßstab		Zeichnungs-Nr.:
Erstel.	20.03.2008	Hamar	DIN ISO 2768 mK	1:2		35-220-040-S
Bearb.	05.12.2019	Seege				
Freig.	09.03.2020	Grind				Vers.Nr.: