




Technical Data:

Case Material	Cover	PA GF black
	Base Plate	PA GF black
	Key Plate	PA GF black
Switch Lever Material		PA GF black
Min. Insulation Resistance		100M Ω
Dielectric Withstanding Voltage		1050V-1min.
Max. Contact Drop During Resistive Load		150mV
Voltage		up to 32VDC
Duty Rating		300A
Overload		1200A-2min.
		1600A-30sec.
		2000A-3sec.
Sealing		IP 67/ IEC 529
Vibration		4G/ 50-2000Hz
Shock G-Level		6G/ 11ms
Weight		325g / 0.72 Pound
Temperature Range		-40°C to +85°C
Wire Section (at nominal Load)		min. 70mm ²
Switch Lever		not removeable
		lockable in "OFF" position
		not lockable in "ON" position
Max. Torque (Main Terminals)		15-20Nm



For this drawing we reserve the copyright
in accordance with DIN ISO 16016

	Date	Name	mm	Scale		Drawing No:
Create	12.07.2006	Grind		1:2		35-314-131-S-900
Edited	07.01.2020	Seegre	General Tolerances			
Check	10.03.2020	Grind	DIN ISO 2768 cL			NSN: