






THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
C		ECR-18-017776	06SEP2019	VS DB

CERTIFICATION: UL & CUL FILE NO. E87824						
PRIMARY			SECONDARY			
TERMINAL NO.	1	2	3	TERMINAL NO.	6	7
VOLTAGE	COM	208	240	VOLTAGE	24	VAC
TERM. WIDTH	.250	.250	.250	TERM. WIDTH	.250	.250
TERM. THICKNESS	.032	.032	.032	TERM. THICKNESS	.032	.032



1. WINDING PROTECTION: INHERENTLY LIMITING.



PACKAGED	DESCRIPTIVE PART NO.	TE PART NO.	PART REV
BULK	4000-09E07AE999	9-1611454-6	C
INDIVIDUAL	4000Y09E07AE999	1-1611457-7	C

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 13NOV2018 VIC SLACK	TE Connectivity	
DIMENSIONS: INCHES		CHK 13NOV2018 D. BLOESCH		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 24JAN2013 D. BLOESCH	NAME TRANSFORMER OUTLINE	
0 PLC ±- 1 PLC ±.1 2 PLC ±.03 3 PLC ±.015 4 PLC ±- ANGLES ±-		PRODUCT SPEC	RESTRICTED TO	
MATERIAL		APPLICATION SPEC	SIZE A3	CAGE CODE 00779
FINISH		WEIGHT	DRAWING NO. 4000_09E07AE999	
		CUSTOMER DRAWING	SCALE 1:1	SHEET 1 OF 1
				REV C