




LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	DWN
			A	DRAWN	21JUL05	JR
						APVD
						EH

- 1 OPERATION TEMPERATURE IS 105° C MAX.
- 2 RETENTION FORCE — 16 OUNCES MIN INITALLY.
6 OUNCES MIN AFTER 500 CYCLES.
- 3 REFER TO MOUNTING HOLE PATTERN.
- 4

 .175 MAX TO BE MEASURED ACROSS THE CUT-OFF TABS.



RECOMMENDED MOUNTING
HOLE PATTERN

NYLON 6/6; VIOLET		BRASS – TIN / NICKEL		1–521800–7	
NYLON 6/6; RED		BRASS – TIN / NICKEL		1–521800–2	
NYLON 6/6; BLACK		BRASS – TIN / NICKEL		1–521800–0	
HOUSING – MATERIAL; COLOR		RECEPTACLE – MATERIAL; FINISH		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 21JUL05		<div><div><div>tyco</div><div>Electronics</div></div><div>Tyco Electronics Corporation Harrisburg, Pa 17105–3608</div></div>	
DIMENSIONS: <div><div><div>mm</div><div>[INCHES]</div></div></div>		CHK E. HOWARD 21JUL05			
<div><div><div>⊕</div><div>⊕</div></div></div>		APVD E. HOWARD 21JUL05		NAME ASSEMBLY, TEST PROBE	
		PRODUCT SPEC —		—	
MATERIAL SEE TABLE		APPLICATION SPEC —		SIZE A2	
		WEIGHT —		CAGE CODE 00779	
FINISH SEE TABLE		CUSTOMER DRAWING		DRAWING NO C=521800	
		SCALE 6:1		RESTRICTED TO —	
				SHEET 1	
				OF 1	
				REV A	