

LOW PROFILE 2 POSITION CONNECTOR

TE Connectivity (TE)'s Low Profile 2 Position Connectors are highly suitable for ultra-thin, high current display applications, across a wide range of uses, from TVs and major home appliances, to HVAC and industrial control boards, among others. Low Profile 2P connector has total mating height within 6mm and operating current up to 15A. Low Profile 2P Connector can be used in reflow and wave soldering to support a wide range of application requirements.

ELECTRICAL

- 15A Max/pin
- Voltage Rating: 600V AC

MECHANICAL

- Locking Force: 67N min/2P
- Retention Force: 45N min/2P
- Insertion Force: 45N max/2P

MATERIALS

- Housing flammability ratings: UL 94 V-0 and GWT*

STANDARDS & SPECIFICATIONS

- UL1977
- Product specification: [108-162069](#)
Low Profile 2 Position Connector
- Application specification: [114-106568](#)
X-LIF F-Spring Positive Lock Receptacles

KEY FEATURES

- Available in both THR and THT soldering for diverse application scenarios
- Compact low profile design with 6mm and high operation current up to 15A
- Low insertion force design helps enable efficient and reliable assembly

APPLICATIONS



Major Home
Appliances



HVAC



Diagnostic
Equipment



Industrial
Panels

*GWT refers to glow wire testing. For more information on glow wire testing please review the white paper [Glow Wire Testing for the Appliance Industry](#) or visit the [Glow Wire Capable Connectors product page](#)

TAB HOLDER




Part Number	Description
2497137-1	250 TAB HOLDER. 2P.12MM THT R-A
2497137-2	250 TAB HOLDER. 2P.12MM THR R-A

HOUSING

Part Number	Description
2498098-1	250 HSG. F-SPRING REC. 12MM 2P BLK

CONTACT

Part Number	Description	Mating Force
2379911-1	250 FSPRING REC. 18-14AWG TPBR	15N max
2379911-6	250 FSPRING REC. 18-14AWG TPBR	20N max



Connect With Us

We make it easy to connect with our experts and are ready to provide all the support you need.
Visit te.com/support to chat with a Product Information Specialist.

TE Connectivity
Connected Living Solutions

te.com/low-profile-2-position-connector

TE, TE Connectivity, TE connectivity (logo), Positive Lock and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any changes to the information contained herein without prior notice. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use, or misapplication of the product. TE expressly disclaims any implied warranties with respect to the information contained herein, including, but not limited to, implied warranties of merchantability or fitness for a particular purpose. Dimensions, specifications and/or information contained herein are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions, specifications and/or information. Users of TE Connectivity products must make their own assessment as to whether the respective product is suitable for the respective desired application.

© 2025 TE Connectivity. All Rights Reserved.

12-25