


RECOMMENDED MOUNTING HOLE PATTERN FOR .063 THICK P.C. BOARD

- 1 MATERIAL:  
 BASE: THERMOPLASTIC POLYESTER, UL 94V-0 (NATURAL).  
 POST: COPPER ALLOY ( TIN OR TIN-PLATED, .000150" MIN THICK-SEE PART NUMBER TABLE FOR DETAILS ).
- 2 ONE HOLE MAY BE UNDERSIZED (.032-.035 DIA) FOR ASSEMBLY RETENTION DURING WAVE SOLDERING.
- 3. PARTS MUST COMPLY WITH AMP SOLDERABILITY SPEC 109-11-2.
- 4 PLASTIC AROUND POST PERMISSIBLE IN THIS AREA ONLY.
- 5 DIMENSION APPLIES WHEN HEADER IS HELD FLAT.
- 6 MEASURED AT -A-
- 7 COORDINATE DIMENSION APPLIES FROM CENTER OF ACTUAL FEATURE.
- 8 RADIUS AT TIP PERMITTED, BOTH ENDS.
- 9 POST MUST WITHSTAND 3.0 LB MIN AXIAL FORCE IN BOTH DIRECTIONS WITHOUT DISLODGING.
- 10 SOLDER SIDE OF BOARD IS SHOWN.
- 11 DIMENSION SHOULD BE .060 MIN WHEN MATING WITH A MTA-100 CONNECTOR ASSEMBLY OR A CST-100 CONNECTOR.
- 12 HOLE IN OMITTED POST LOCATION MAY NOT BE PRESENT.
- 13. AMP LOGO MAY OR MAY NOT APPEAR ON MOLDING HOUSING.

.035	0.89	1.000	25.40
.032	0.81	.505	12.83
.0250	0.635	.488	12.40
.025	0.64	.295	7.49
.020	0.51	.200	5.08
.010	0.25	.110	2.79
.008	0.20	.100	2.54
.005	0.13	.092	2.34
.004	0.10	.063	1.60
.003	0.08	.060	1.52
.0015	0.038	.050	1.27
.0010	0.025	.044	1.12
.000150	0.0038	.040	1.02
IN	MM	IN	MM

CONVERSION TABLE

SUPERSEDED BY 3-644454-1	TIN	4	3-644454-1
	TIN-LEAD	4	644454-1
	FINISH	POST NO. OMITTED	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG: VISWESWARA 07JULY2005	Tyco Electronics Corporation Harrisburg, Pa 17105-3608
DIMENSIONS: INCHES		CHK: D. BOSSI 07JULY2005	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPROD: D. BOSSI 07JULY2005	NAME: MTA-100 HEADER ASSEMBLY, NARROW, .025 SQUARE STRAIGHT POST, TIN PLATED, 5 POSITION, OMITTED POST
0 PLC ± -		PRODUCT SPEC: 108-1050	SIZE: A1
1 PLC ± -		APPLICATION SPEC: -	SCALE: 10:1
2 PLC ± -		WEIGHT: -	SHEET 1 OF 1
3 PLC ± -		CUSTOMER DRAWING	REV F1
4 PLC ± -		SCALE: 10:1	
ANGLES ± -			
FINISH: -			