



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		B		REVISED PER ECO-12-012205	06DEC2012	KH	DO
		B1		REV PER ECR-13-010313	26JUN2013	ML	SZ



- CABLE LENGTH TOLERANCE = 0.2% OF TOTAL CABLE LENGTH WITH A MIN. TOLERANCE OF ±3.18
I.E. 6096 * .002 = ±12.2
- △ LABEL APPROXIMATELY AS SHOWN PER TEC 2480.0903.MPI
- BECAUSE OF SHIPPING CONSTRAINTS, REFOLDING/SHAPING OF CABLE ASSEMBLIES MAY BE REQUIRED BY CUSTOMER BEFORE INSTALLATION
- HEAT SHRINK SHOULD END 6.0 INCH FROM CONNECTORS TO BOTH ENDS OF THE CABLE.

SOLID	0.50	766682-1
STYLE	CONDUCTOR THICKNESS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. GRZYBOWSKI 03FEB2011	TE Connectivity	
DIMENSIONS: mm		CHK M. SYKES 03FEB2011		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. SYKES 03FEB2011	NAME CABLE ASSEMBLY AMPOWER WAVE CRIMP SYSTEM	
0 PLC ±0		PRODUCT SPEC	SIZE	
1 PLC ±0.5		APPLICATION SPEC	CAGE CODE	
2 PLC ±0.25		WEIGHT	DRAWING NO	
3 PLC ±		Customer Drawing	A200779C-766682	
4 PLC ±		SCALE 2:1	RESTRICTED TO	
ANGLES ±		SHEET 1 OF 1	REV B1	
FINISH ±				