

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F2	REVISED BY ECO 16-008371	25JULY2016	HC	WLS
	F3	REVISED PER ECN-21-102498	16APR2021	WLS	BHC


1 - ESPESSURA DE PAREDES NAO ESPECIFICADAS 0,6.
ALL UNSPECIFIED WALL THICKNESSES 0,6.

2 - INTERCAMBIÁVEL COM PN 180900.
INTERCHANGEABLE WITH PN 180900.

△ 3 - MATÉRIA PRIMA CONFORME ESPECIFICAÇÃO IEC 60335-1, GWT 750°C, SEM CHAMA.
RAW MATERIAL ACC. TO SPEC. IEC 60335-1, GWT 750°C, WITHOUT FLAME.

SECTION A-A

NATURAL	△ 3 NYLON 6.6 V-0	2 - 880110 - 0
NATURAL / NATURAL	NYLON 6.6	880110 - 0
COLOR	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.R.BRIZ 19NOV99	 TE Connectivity	
DIMENSIONS: mm		CHK P.L.FARIA		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD F.ALEXANDRONI	NAME HSG. 4 POSITION, FAST-IN-ON RCPT.	
0 PLC ±-		PRODUCT SPEC	-	
1 PLC ±0,5		APPLICATION SPEC	-	
2 PLC ±-		WEIGHT	-	
3 PLC ±-		SIZE	A3	00779
4 PLC ±-		CAGE CODE	C-880110	
ANGLES ±1°		DRAWING NO	-	
FINISH		RESTRICTED TO	-	
MATERIAL SEE TABLE		CUSTOMER DRAWING	SCALE	2:1
			SHEET	1 OF 1
			REV	F3

1470-19 (3/13)