

617 Receptacle

speedtec - ready

17-pin insulation insert Code 1 Connection Cross Section to 0,5 mm² flange mount /Flange 21x21 Anti-vibration o-ring

A EG A 874 NN 00 00 150A 000 A E A 874 N 00 00 150A 000



Contact Arrangement mating view



© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.


While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH Bernrieder Straße 15 94559 Niederwinkling, Deutschland Tel: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mail: intercontec@te.com Web: www.intercontec.biz

23.07.2018

ssue:





Main Dimensions Receptacle

*for max. wire cross-section pay attention to the cross-section of used contacts

rated voltage rated insulation voltage (L-L)

Data according to VDE 0110/EN61984, Paragraph 6.19.2.2 3 III

2000 m

17

signal max. 3,6 A* 63 V (AC/DC)

1500 V

500

-20 °C to 130 °C when connected IP 66/67

pollution degree over voltage category max. height for operation

Technical Data

number of pins

protection type **Electrical Data**

rated current

mating cycles

temperature range

Material

housina insulation insert seals

zinc diecast / nickel plated PBT, UL 94 / V0 FKM

Contacts (not part of product contents)

Tools (not part of product contents)