TH 025 CONNECTOR SERIES

for the Automotive Industry





TH 025 CONNECTOR SERIES

for the Automotive Industry

High density in limited spaces



Product Features

- TH 025 connectors were designed to provide better connections and performance while securing higher density in limited spaces as required in advanced electronic automotive control systems.
- Another feature is a special contact design to resist fretting corrosion effectively while employing a lower contact force. As a result, the low insertion force of TH 025 connectors allows a lower connector mating force while offering high density for easy handling.
- This small pitch can help customers to reduce space and weight.
- TH 025 connectors feature a pitch of just 2.2mm, compared to the current standard pitch of 2.54mm.
- TH 025 connector series have been originally designed in Japan. An European version has been implemented, in order to fulfill the European customer requirements as:
 - Mechanical coding
 - Color coding
 - Reflow leadfree process for headers
- TH European connectors are available in a full range from 4 to 40 positions.

Applications

- Wire-to-Wire, Wire-to-Board and ECU Applications
 - Mirror
 - Multimedia applications
 - Display screens
 - Airbag ECU / Safety applications
 - Switches
 - Hand free cellphone
 - Immobilizer
 - Dashboard
 - Safety applications
 - Electrically controlled trunk lid latch
 - Tyre pressure monitoring system
 - · Body controller management

Technical Features

- One piece contact designed to minimize fretting corrosion
- Terminal lance design to optimize cavity dimension

TH 025 Receptacle Contacts 0.635 x 0.635mm

Insertion Force 2.2 N max.

Contact Force

2.8 N (at an early stage), 2.0 N (after ageing)

Current Carrying Capacity

5 A (to 7 A within some conditions)

Wire Size Range

from 0.13 to 0.5mm 2 ,

specific 0.75mm² application possible

Contact Finish

- for Receptacle

Tin and gold plating

for TabTin plating

Material

– for Receptacle

Copper Alloy

– for Tab Brass Temperature Range


 $-40\,^{\circ}\text{C}$ up to +105 $^{\circ}\text{C}$


Contact Retention Force 100 N (retainer block)

Product Specification 108-5668 & 108-15299

Application Specification

114-5250 & 114-15120 (for ISO wire)





Receptacle Contacts

Wire Size	Insulation	Material	Part Numbers					
Range (mm²)	Diameter (mm)	and Finish	Strip Form	Package Quantity	Applicator	Hand Tool	Extraction Tool	
0.13-0.22	0.90-1.05	Copper alloy, pre-tin plated	2005097-1	10,000	x-2151966-x	7-1579014-1	-	
0.22-0.50	1.10-1.60	Copper alloy, pre-tin plated	1123343-1	10,000	x-2151494-x	7-1579014-2	1276565-1 •)	
0.22-0.50	1.10-1.60	Gold plated (0.8 µm)	1801069-2	10,000	on request	-	-	
0.22-0.50	1.10-1.60	Gold plated (0.38 µm)	1123343-2	10,000	x-2151494-x	7-1579014-2	1276565-1 •)	
0.50-0.75**)	1.30-1.60	Gold plated (0.8 µm)	1801248-2*)	10,000	on request	-	-	

^{**)} Recommended for airbag applications (0.5mm²)

Tab Contacts

Wire Size	Insulation	Material	Part Numbers					
Range (mm²)	Diameter (mm)	and Finish	Strip Form	Package Quantity	Applicator	Hand Tool	Extraction Tool	
0.13-0.22	0.90-1.05	Brass, tin plated	2005098-1	10,000	x-2151966-x	7-1579014-1	-	
0.22-0.50	1.10-1.60	Brass, tin plated	1674742-1	10,000	x-2151216-x	7-1579014-3	1579007-8 •)	

^{•)} Depending on the assembly of contact and housing

^{**)0.75}mm² – Application depending on wire function

^{◆)}Depending on the assembly of contact and housing

Receptacle Housings

All products are 2 row with the exception of the 4P which is a single row

Technical Features

- Compact design with 2.2mm pitch
- Two parts (housing + retainer block = 1 piece) 4P only – is single piece with hinged Lid

-40°C up to +105°C Temperature range Secondary lock Housing retainer block Dielectric strength 1000 V AC 1 min Insulation resistance > $100\,\mathrm{M}\Omega$ Housing material PBT Connector mating force Max 60 N **Product specification** 108-15299 Application specification 411-15672

Tab Housings

All products are 2 row with the exception of the 4P which is a single row

Technical Features

- Compact design with 2.2mm pitch
- Two parts (housing + retainer block = 1 piece)
 4P only is single piece with hinged lid
 8P only Japanese version

Temperature range-40° C up to +105° CSecondary lockHousing retainer blockDielectric strength1000 V AC 1 minInsulation resistance> 100 MΩHousing materialPBTConnector mating forceMax 60 N

 Product specification
 108-15299 / 108-5787*)

 Application specification
 411-15672 / 411-78011*)

*) Japanese version

Receptacle Housing		Tab Ho	Tab Housing		
	1379658-1		1379674-1		
	1379658-2		1379674-2		
Rec 4P1row	1379658-3	Tab 4P1 row	1379674-3		
	1379658-4		1379674-4		
	1-1379658-1		1-1379674-1		
	1379659-1	Tab 8P 2 row	1565804-1		
	1379659-2	IdD 8P Z IOW	1565804-2		
Rec 8P 2 row	1379659-3				
	1379659-4				
	1379659-5				
	1379662-1		1379675-1		
	1379662-2		1379675-2		
Rec 12P 2 row	1379662-3	Tab 12P 2 row	1379675-3		
	1379662-4		1379675-4		
	1379662-5		1379675-5		
	1379665-1		1379678-1		
	1379665-2	Tab 16P 2 row	1379678-2		
Rec 16P 2 row	1379665-3	14D 16P 2 TOW	1379678-3		
	1379665-4		1379678-4		
	1379665-5				
	1379668-1		1379681-1		
	1379668-2	Tab 2/D 2	1379681-2		
Rec 24P 2 row	1379668-3	Tab 24P 2 row	1379681-3		
	1379668-4		1379681-4		
	1379668-5				
	1379671-1				
	1379671-2				
Rec 40P 2 row	1379671-3				
	1379671-4				
	1379671-5				

TE CONNECTIVITY ONLINE

TE.com offers an enhanced digital experience, with more than 250,000 parts profiled. The site has deep, rich product data and easier access to tools and services. Other offerings include improved search and navigation and knowledge and idea sharing.



LITERATURE

TE.com offers a variety of product-specific catalogs, brochures, white papers and other technical information. To download our literature visit www.te.com/usa-en/industries/automotive/automotiveliterature.html



PRODUCT INFORMATION

Search for a specific product by category, part number or document number.

www.TE.com



STAY CONNECTED

You can rely on TE's PIC Team to answer your general or technical questions. To contact a PIC representative, visit

www.TE.com/support-center



TE Connectivity Germany GmbH

Ampèrestrasse 12-14 64625 Bensheim Germany

Phone: +49 (0)6251133-0 Fax: +49 (0)6251133-1600

TE Connectivity Germany GmbH certified acc. ISO 14001 and ISO/TS 16949:2002 © 2015 TE Connectivity family of companies. All rights reserved.

TE, TE Connectivity, and TE connectivity (logo) are trademarks.

TE Connectivity's (TE's) only obligations are those stated in TE's General Terms and Conditions of Business (www.te.com/aboutus/tandc.asp). TE expressly disclaims any implied warranty regarding the information contained herein, including, but not limited to, the implied warranties of merchantability or fitness for a particular purpose.

1654393-1 | Published 09-2015

