

## 617 Receptacle angled rotatable **speedtec** - ready

17-pin insulation insert Code 1 Connection Cross Section to 0.5 mm<sup>2</sup>

flange mount /Flange 21x21

## A ED C 874 NN 00 00 150A 000 A G C 874 N 00 00 150A 000



**Contact Arrangement** mating view



zinc diecast / chromated

Contacts (not part of product contents)

Tools (not part of product contents)


© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH Bernrieder Straße 15 94559 Niederwinkling, Deutschland Tel.: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mail: intercontec@te.com Web: www.intercontec.biz





Main Dimensions Receptacle angled rotatable

\*for max. wire cross-section pay attention to the cross-section of used contacts

**Technical Data** number of pins temperature range protection type

**Electrical Data** rated current rated voltage rated insulation voltage (L-L) signal max. 3.6 A\* 63 V (AC/DC) 1500 V

-20 °C to 130 °C when connected IP 66/67

17

## Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

3 III 2000 m

FKM

PBT, UL 94 / V0

500

Material

housing insulation insert seals

mating cycles

pollution degree

over voltage category max. height for operation