

623

speedtec - ready

17-pin insulation insert uncoded EMC - Shielding

A KU A 034 NN 00 73 0255 000 A K A 034 N 00 73 0255 000



Contact Arrangement mating view



Material

housing insulation insert seals clamp ring

pollution degree over voltage category

max. height for operation

Technical Data

rated voltage rated insulation voltage (L-L)

number of pins temperature range

clamping range

protection type
Electrical Data

rated current

mating cycles

zinc diecast / nickel plated PBT, UL 94 / V0 FKM brass / nickel plated

17

signal max. 7 A* 125 V (AC/DC) 2000 V

500

3 III

Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

2000 m

-20 °C to 130 °C

Ø 9.0 mm to Ø 14.3 mm when connected IP 66/67

Contacts (not part of product contents)

Tools (not part of product contents)

© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without to the latest dimensions and design specifications.

TE Connectivity Industrial GmbH Bernrieder Straße 15 94559 Niederwinkling, Deutschland Tel.: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mail: intercontec@te.com Web: www.intercontec.biz

ssue: 29.08.2018





Main Dimensions

*for max. wire cross-section pay attention to the cross-section of used contacts