112G PORTFOLIO SOLUTIONS

TE Connectivity's (TE) 112G wide-ranging product portfolio provides a robust and flexible array of solutions to enable next generation architectures. The product family supports standard form-factors and performance requirements, designed with reliability and upgradability in mind, enabling applications including compute/storage, high-speed networking and machine learning/ artificial intelligence.

Key Benefits

- Due to the demands on next generation high-speed designs, TE Connectivity (TE) has developed one of the most comprehensive, flexible and high-performing internal and external connector and cable assembly portfolios in the market
- Next generation products aligned with or exceeding the industry's 112G channel performance needs, delivering high marks in cross talk, return loss, and insertion loss performance
- Standard external input/output (I/O) form factors enable ecosystem connectivity for intra-rack and inter-rack applications
- Copper cable solutions provide cost-effective system design and connectivity options to achieve the performance demands of 112G architectures

Products

- **112G Product Support for SFP, QSFP, QSFP-DD and OSFP Interconnects**
  - Active Copper Cables (ACC)
  - Direct Attached Copper Cables (DAC)
  - I/O Connectors and Cages
- **STRADA Whisper Connectors, Cages, and Cable Assemblies / STRADA Whisper Absolute Connectors**
- **Over the Board (OTB) I/O Solutions**
- **Enabling 112G Through PCIe**
  - CEM Connectors
  - Sliver Product Family (SFF-TA-1002/SFF-TA-1020)
  - MCIO Product Family (SFF-TA-1016)
- **MULTI-BEAM and Busbar Power Connectors and Assemblies**

112G Portfolio Solutions

112G Per Lane I/O Solutions

- TE is on the leading edge of developing 112G per lane solutions for 800G and lower aggregate port bandwidths. Our designs are MSA specification compliant and deliver high performance

- Thermal management is becoming challenging across high speed IO connectors. TE has a wide portfolio of cage designs and mounts to fit various forced air and liquid cooling architectures dissipating 25W+ powers

- Offerings: OSFP, QSFP-DD, QSFP, SFP, SFP-DD, CDFP compliant products

Cabled STRADA Whisper Backplane Connectors

- Flexible solution to run longer channels

- Support 112G PAM4 and 56G NRZ

- Excellent EMI performance

- Cable receptacle also available

Sliver Interconnects for SFF-TA-1002

- The Sliver connector design was adopted as the standard connector design in the SFF-TA-1002 specification which was adopted in reference applications by OCP, EDSFF and Gen-Z

- Chosen for performance, density, flexibility and robustness

- Offerings: mid-board connectors, card edge connectors and cable assemblies

Sliver Internal Cabled Interconnects

- Slim interface supports wide variety of protocols

- Rated up to 112G PAM4 and 56G NRZ

- Sliver products comply with SFF-TA-1002 specification

112G Portfolio Solutions

Mini-SAS HD Connectors and Cable Assemblies

- Industry-proven solution to address SFF-8-86, 887, and 8088 standards
- Supports SAS 2.0, SAS 2.1, SAS 3 and PCIe applications
- Supports PCIe4 16G applications

Busbar Power Connectors

- Solutions for power delivery in server, switch, wireless, industrial control and modular power supplies. Commonly used in rack-mounted equipment with busbar architecture
- Benefits: Reliable, Low resistance, Robust
- Applications: IT Tray, Cubby Shelf, Battery Backup Unit (BBU) and Power Shelf

Busbar Power Assemblies

- Solutions for 12V and 48V requirements
- Benefits: reliable and robust power delivery
- Offerings: flexible, rigid, and laminated busbars
- End to end solution for power distribution and PCB interconnection

Product Interconnectivity

INTERNAL CARD EDGE CABLES & CONNECTORS

SLIVER INTERCONNECTS
FOR SFF-TA-1002

MCIO & SLIMSAS
CONNECTORS &
CABLE ASSEMBLIES

SLIVER INTERNAL CABLE
INTERCONNECTS

HIGH SPEED I/O INTERCONNECTS

OSFP INTERCONNECT

ZSFP+ / SFP56
INTERCONNECTS

QSFP INTERCONNECTS

QSFP-DD INTERCONNECTS

POWER CONNECTORS & CABLE ASSEMBLIES

CROWN CLIP JUNIOR
BUSBAR CONNECTORS

ELCON MINI
CONNECTORS

MULTI-BEAM XLE
CONNECTORS

HIGH SPEED BACKPLANE CONNECTORS

STRADA WHISPER
CONNECTOR FAMILY

HYBRID CABLE ASSEMBLIES

SLIVER CABLE
ASSEMBLIES

STRADA WHISPER
CABLED RECEPTACLE

POWER CONNECTORS & CABLE ASSEMBLIES

CROWN CLIP JUNIOR
BUSBAR CONNECTORS

ELCON MINI
CONNECTORS

MULTI-BEAM XLE
CONNECTORS

HYBRID CABLE ASSEMBLIES

SLIVER CABLE
ASSEMBLIES

STRADA WHISPER
CABLED RECEPTACLE

HIGH SPEED I/O INTERCONNECTS

CABLE ASSEMBLIES

ZSFP+ / SFP56
INTERCONNECTS

QSFP INTERCONNECTS

OSFP INTERCONNECT

INTERNAL CARD EDGE CABLES & CONNECTORS

SLIVER INTERCONNECTS
FOR SFF-TA-1002

MCIO & SLIMSAS
CONNECTORS &
CABLE ASSEMBLIES

SLIVER INTERNAL CABLE
INTERCONNECTS

te.com

CROWN CLIP, ELCON Mini, STRADA Whisper, Sliver, MULTI-BEAM XLE, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products zSFP+ and zQSFP+ are part of the ZXP family of products and use ZXP technology. ZXP is a trademark of Molex LLC, MCIO is a trademark of Amphenol. and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

©2022 TE Connectivity. All Rights Reserved.

04/22   Original

TE TECHNICAL SUPPORT CENTER

USA:	1.800.522.6752
Canada:	1 .905.475.6222
Mexico:	52.0.55.1106.0800
Latin/S. America:	54.0.11.4733.2200
Germany:	49.0.6251.133.1999
UK:	44.0.800.267666
France:	33.0.1.3420.8686
Netherlands:	31.0.73.6246.999
China:	86.0.400.820.6015