

DRAWING NO FGD1085-1170-7-C


THIS DRAWING IS A CONTROLLED DOCUMENT



**CATALOGUE NUMBER: FGD1085-1170-7  
SUITS CONDUCTOR**

**DEADEND**


STRANDING	COND. TYPE	DIAMETER	FITTING LAY
7/3.75	SC/GZ	11.25	RIGHT HAND




**TECHNICAL SPECIFICATIONS:**

CATALOGUE NUMBER: FGD1085-1170-7  
 DESCRIPTION: FULL-TENSION GALVANISED STEEL DEADEND  
 MATERIAL: HEAVILY GALVANISED STEEL WIRE  
 NUMBER OF RODS: 6  
 ROD DIAMETER: 2.95mm  
 OVERAL LENGTH: 930mm  
 END FINISH: CHAMFERED  
 FITTING LAY DIRECTION: RIGHT HAND  
 COLOUR CODED: BLACK

**PRODUCT LABEL**



**BOX LABEL**



THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TE CONNECTIVITY PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TE CONNECTIVITY CORPORATION, AUSTRALIA.

LOC							IMPLIED NOTES BURRS AND SHARP EDGES REMOVED SCREW THREADS ARE TO AS 1275 DO NOT WORK TO DIMS MARKED REF SURFACE FINISH 6.3 U.N.O. DIMS ARE IN mm. DO NOT SCALE	IMPLIED TOLERANCES HOLE DIA AND LOCATIONS: ±0.5mm. DIMENSIONS UP TO 30mm: ±1.5mm. DIMENSIONS OVER 30mm: ±5% UP TO A MAX OF: ±5mm. ANGULAR DIMENSIONS: ±5°	TCPN -	PART Alias UTX/DUL FGD1085-1170-7	TITLE FULL-TENSION GALVANISED STEEL DEADEND (FGD) FITTING COND. RANGE: Ø10.85-Ø11.70 7/3.75 SC/GZ					
DIST	—	I	NEW RELEASE	14-05-2013	RN	AT	MATERIAL DESC HEAVILY GALVANISED STEEL WIRE	MATERIAL NO -	MATL SPEC/STD/DRG NO -	PROCESS SPEC HEAT TREAT/PLATING NO -	Cat No FGD1085-1170-7	DRAWN RN	DATE 14-05-2013	TE Connectivity 2/3 Corella Close Berkeley Vale NSW 2261 Australia		
POS	REV	REVISION RECORD		DATE	DWN	APVD	MATERIAL NO	MATL SPEC/STD/DRG NO	PROCESS SPEC HEAT TREAT/PLATING NO	SIZE A3	PROJECTION 3RD ANGLE	SCALE NTS	DRAWING NO FGD1085-1170-7-C	SHEET 1	OF 1	REV 1

Format: generic\_m03.au.r1.fm 4

Template: tec\_generic\_a3\_metric.au.r1.drw 3

Dwg No from P1 Mod Fam Tbl: 2 >AUXXXXX